



High-Efficiency Fine Tip (#7545-100)

High-Efficiency tips reach soldering temperature in less than 10 seconds and reach a tip temperature of approximately 900°F.



The High-Efficiency Fine Tip diameter is 1/16" or .063". High-Efficiency Tips heat up faster and provide 20% more soldering time than our standard tips. Tips reach soldering temperature in less than 10 seconds and reach temperature of approximately 900°F.