


Network Wiring Modular Jacks

Category 6, 5e and USOC 6-Position

Termination Towers-
Quick termination and exceptional strain relief.

Nose Contacts-
Increases performance and controls crosstalk.

Dust Cover-
(Optional) protects port and accepts Hubbell Icons.



Stuffer Cap-
Secures strain relief and acts as a termination base.

Universal Wiring-
Easy-to-follow, eliminates wiring confusion.

Technical Specifications

- Nose Contacts - High-performance copper alloy contacts, 50 micro-inch. gold plating to FCC 47 Part 68.5 subpart F.
- IDC 110 Contacts - Phosphor Bronze base metal with 100 micro-inch tin/lead 60/40 plating over nickel under plating.

Verifications

- Category 6 component compliance.
- Category 5e component performance.
- ANSI/TIA/EIA-568-B Category 5e and 6 component.
- UL Listed 1863.
- CSA Certified.
- FCC part 68.5, subpart F compliant.
- IEC-603-7 compliant.
- ETL Verified.

When network convergence is the protocol, Hubbell HBL5E and HBL6 jacks deliver unmatched industry component performance providing maximum bandwidth for all of your LAN, multimedia and PoEP (power over ethernet protocol) applications.



The HBL6 modular jack provides Category 6 component performance allowing for support of emerging applications.

The HBL5E modular jacks deliver performance far surpassing ANSI/TIA/EIA - 568-B Category 5e component requirements.

The HBLU 6-position USOC modular jack supports all low-speed data and voice-grade applications.

All three jack families feature a quick termination process that ensures a reliable termination every time.

HBL Series Category 6, 5e and USOC 6-Position Jacks

Color	Catalog Numbers		
	Category 6	Category 5e	USOC
Black	HBL6BK	HBL5EBK	HBLUBK
Blue	HBL6B	HBL5EB	HBLUB
Electric Ivory	HBL6EI	HBL5EEI	HBLUEI
Gray	HBL6GY	HBL5EGY	HBLUGY
Green	HBL6GN	HBL5EGN	HBLUGN
Office White	HBL6OW	HBL5EOW	HBLUOW
Orange	HBL6OR	HBL5EOR	HBLUOR
Red	HBL6R	HBL5ER	HBLUR
Telco Ivory	HBL6TI	HBL5ETI	HBLUTI
White	HBL6W	HBL5EW	HBLUW
Yellow	HBL6Y	HBL5EY	HBLUY