

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010101051](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: KK PC Board Connector, Right-Angle Mount Style A, 1.00µm Tin (Sn), 5 Circuits

Documents:

[3D Model](#) [Product Specification PS-99020-0087-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Receptacles
 Series [3002](#)
 Application Board-to-Board, Power
 Overview [KK 508 Connector System](#)
 Product Name KK 508
 UPC 800753744288

Physical

Circuits (Loaded) 5
 Circuits (maximum) 5
 Color - Resin Natural
 Durability (mating cycles max) 25
 Flammability 94V-2
 Glow-Wire Capable No
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 1.500/g
 Number of Rows 1
 Orientation Right Angle
 PC Tail Length 4.30mm
 PCB Locator No
 PCB Retention Yes
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 5.08mm
 Pitch - Termination Interface 5.08mm
 Plating min - Mating 1.016µm
 Plating min - Termination 1.016µm
 Polarized to PCB Yes
 Temperature Range - Operating See Product Specification
 Termination Interface: Style Through Hole

Electrical


Current - Maximum per Contact 7.0A
 Voltage - Maximum 250V

Solder Process Data

Lead-freeProcess Capability WAVE

Material Info

Engineering Number 300205A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3002](#) Series

Mates With

Headers [3003](#) , [2599](#) , [3061](#)

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-99020-0087-001

SDAE-3002-NA-*

This document was generated on 10/04/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION