

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1706731200](#)
Status: **Active**
Overview: [EdgeLine High Speed Connectors](#)
Description: EdgeLine Vertical Connector, 12.5 Gbps, 0.80mm Pitch, 1.57mm PCB Thickness, 1 Bay, 200 Circuits

Documents:

3D Model	Application Specification AS-76693-101-001 (PDF)
Drawing (PDF)	Packaging Specification PK-76693-900 (PDF)
Product Specification PS-75594-999-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-76693-100-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	170673
Application Tooling Part Link	62100-8500
Application Tooling Part Link	62201-8736
Component Type	Edgecard to PCB
Data Rate	12.5-20.0 Gbps
Edge Card Thickness	1.57mm
High Power Bay (30.0A or more)	No
Orientation	Vertical
Overview	EdgeLine High Speed Connectors
Product Name	EdgeLine
Standard Based	General
UPC	884982404564

Physical

(p)ower-(s)ignal Configuration	200s - 0p
Circuit Size Range	65-200 Circuits
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	200
Entry Angle	N/A
Flammability	94V-0
Keying to Mating Part	N/A
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	10.025/g
PCB Locator	No
PCB Thickness - Recommended	2.79mm
Packaging Type	Tray
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[170673 Series](#)

Electrical

Current - Maximum per Contact 1.5A
Voltage - Maximum 250V AC

Solder Process Data

Lead-free Process Capability N/A

Material Info**Reference - Drawing Numbers**

Application Specification AS-76693-100-001, AS-76693-101-001
Electrical Model Document 1706730002-000
Packaging Specification PK-76693-900
Product Specification PS-75594-999-001
Sales Drawing SD-170673-0001, SD-170673-1200
Symbol/Footprint Data SYM-170673-1200

This document was generated on 10/08/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION