

This document was generated on 10/26/2018 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Desit Maria			
Part Numb	er: <u>0430450825</u>		
Status:	Active		
Overview:	Micro-Fit 3.0 Connector \$	System Product Family	
Description: Micro-Fit 3.0 Vertical Heade		ader, 3.00mm Pitch, Dual Row, 8 Circuits, with PCB Press-fit	6 CA
		ld, Glow-Wire Capable, Black	
Docume	nts:		Rot
3D Mode		Product Specification TS-43045-002-001 (PDF)	A Real March
Drawing (-	Product Specification TS-46235-001-001 (PDF)	Constant U
Product Specification PS-43045 (PDF)		Packaging Specification PK-70873-0314-001 (PDF)	Q ·
Product S	Specification PS-43045-001 (PDF)	RoHS Certificate of Compliance (PDF)	Series image - Reference only
Product S	Specification TS-43045-001-001 (PDF)	Product Literature (PDF)	
,			EU ELV
Agency (Certification		Not Relevant
CSA		LR19980	
UL		E29179	EU RoHS China RoHS
			Compliant
General	ite	DCD Headers	REACH SVHC
Product F	anniy	PCB Headers	Not Contained Per -
Series Application		<u>43045</u> Power, Wire-to-Board	ED/61/2018 (27 June 2018)
Comment		"""""""High Temperature/Square Pin/Offset Through	Halogen-Free
Comment		Hole Mounting Solder Type <p><p>This Molex</p></p>	Status
		product is manufactured from material that has the	Low-Halogen
		following ratings, tested by independent agencies:.	For more information, please visit <u>Contact US</u>
		a) A Glow Wire Ignition Temperature (GWIT) of at	
		least 775 deg C per IEC 60695-2-13 b) A Glow	China ROHS Green Image
		Wire Flammability Index (GWFI) above 850 deg C	ELV Not Relevant
		per IEC 60695-2-12.and hence complies with the	RoHS Phthalates Not Contained
		requirements set out in the International Standard IEC	
		60335-1 5th edition - household and similar electrical	
		appliances - safety, section 30 Resistance to heat	Search Parts in this Series
		and fire. <p><p> The customers using this product</p></p>	43045 Series
		must determine its suitability for use in their particular application through testing or other acceptable means	
		as described in end-product glow-wire flammability test	Mates With
		standard IEC 60695-2-11 and any applicable product	Micro-Fit 3.0 Receptacle Housing 43025
		end-use standard(s). <p> If it is determined during</p>	<pre> > Micro-Fit 3.0 TPA Receptacle Housing</pre>
		the customer's evaluation of suitability, that higher	<u>172952</u>
		performance is required, please contact Molex for	
		possible product options.""""""	
Overview	,	Micro-Fit 3.0 Connector System Product Family	
	iterature Order No	987650-5984	
Product N	lame	Micro-Fit 3.0	
UPC		800753822474	
Physical			
Breakawa		No	
Circuits (I		8	
Circuits (maximum)		8	
Color - Resin		Black	
	(mating cycles max)	30	
Flammability		94V-0	
	e Capable	Yes	
Mated He	•	17.64mm	
Material -		Brass	
Material - Plating Mating		Gold	

Material - Plating Termination Material - Resin Net Weight Number of Rows Orientation PCB Locator PCB Retention PCB Thickness - Recommended Packaging Type Pitch - Mating Interface Plating min - Mating Polarized to PCB Shrouded Stackable Surface Mount Compatible (SMC) Temperature Range - Operating Termination Interface: Style	Tin High Temperature Thermoplastic 1.321/g 2 Vertical Yes Yes 1.60mm Tray 3.00mm 0.381µm Yes Fully No Yes -40° to +105°C Through Hole - Kinked Pin		
Electrical Current - Maximum per Contact Voltage - Maximum	8.5A 600V		
Solder Process Data Duration at Max. Process Temperature (seconds) Lead-freeProcess Capability Max. Cycles at Max. Process Temperature Process Temperature max. C	030 SMC&WAVE 003 260		
Material Info			
Reference - Drawing Numbers Packaging Specification Product Specification	PK-70873-0314-001 PS-43045, PS-43045-001, TS-43045-001-001, TS-43045-002-001, TS-46235-001-001 SD-43045-009 SYM-43045-0824, SYM-43045-0824_6		
Sales Drawing Symbol/Footprint Data			

This document was generated on 10/26/2018 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION