



ORDER CODE:  
R40-300XXXX

LENGTH L1 IN mm

PLATING FINISH:  
00 = SELF COLOUR  
02 = NICKEL (F0203)  
17 = PROTECTIVE DIP (F0701)

- NOTES:
- 0.3 CHAMFERS FOR LEAD-IN ON THREADS.
  - REMOVE ALL BURRS.
  - THREADS TO BE MANUFACTURED IN ACCORDANCE WITH BS3643 PT.2 1981.

PART No.	L1	L3 MIN	L4 MAX	S/AREA	PART No.	L1	L3 MIN	L4 MAX	S/AREA
R40-30006XX	6.00	2.50	5.24	422.7	R40-30030XX	30.00	8.00	12.0	1138.9
R40-30007XX	7.00	3.50	6.24	463.2	R40-30035XX	35.00	8.00	12.0	1272.3
R40-30008XX	8.00	4.50	7.24	503.7	R40-30040XX	40.00	8.00	12.0	1405.7
R40-30009XX	9.00	5.50	8.24	544.2	R40-30046XX	46.00	8.00	12.0	1563.3
R40-30010XX	10.00	6.50	9.24	584.6	R40-30063XX	63.00	8.00	12.0	2016.8
R40-30011XX	11.00	8.00	10.24	621.7					
R40-30012XX	12.00	8.00	10.74	658.7					
R40-30013XX	13.00	8.00	12.0	685.4					
R40-30014XX	14.00	8.00	12.0	712.1					
R40-30015XX	15.00	8.00	12.0	738.8					
R40-30016XX	16.00	8.00	12.0	765.4					
R40-30018XX	18.00	8.00	12.0	818.8					
R40-30020XX	20.00	8.00	12.0	872.1					
R40-30025XX	25.00	8.00	12.0	1005.5					

3	12.10.95	3750
2	29.11.90	1734
1	27.09.89	----
ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN: W. BOURNE		
CUSTOMER REF.		
ASSEMBLY DRG:		



HARWIN INC USA TEL: (812) 285 0055 FAX: (812) 285 0056	HARWIN PLC UK TEL: (01705) 370451 FAX: (01705) 324010	HARWIN PTE SINGAPORE TEL: 7794909 FAX: 7793868
---	--	---

TOLERANCES  
X. = ±1mm  
XX = ±0.25mm  
XXX = ±0.10mm  
XXXX = ±0.01mm  
ANGLES = ±1'  
UNLESS STATED

MATERIAL:  
BRASS CZ121 TO BS2874

FINISH: SEE ABOVE

S/AREA: SEE TABLE mm<sup>2</sup>

TITLE:  
M4 HEXAGONAL  
MALE/FEMALE SPACER

DRAWING NUMBER:  
R40-300XXXX

SHT  
1 OF 1