

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0526102033

Status:

Active

Overview:

FFC-FPC (SMT)

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 20 Circuits, Tin-Silver-Bismuth

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-52610-032-001 \(PDF\)](#)
- [Packaging Specification SPK-52610-003-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

FFC/FPC Connectors

Series

52610

Overview

FFC-FPC (SMT)

Product Name

Easy-On

Series Name

Slider

UPC

887191316215

Physical

Actuator Type

Slider

Circuits (Loaded)

20

Color - Resin

Natural

Contact Position

N/A

Durability (mating cycles max)

30

Flammability

94V-0

Mated Height

5.75mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Silver, Tin-Bismuth

Material - Plating Termination

Silver, Tin-Bismuth

Material - Resin

Nylon

Net Weight

931.500/mg

Number of Rows

1

Orientation

Vertical

PC Tail Length

2.00mm

PCB Locator

No

PCB Mounting

Surface Mount

PCB Retention

None

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

1.00mm

Pitch - Termination Interface

1.00mm

Polarized to PCB

No

Stackable

No

Temperature Range - Operating

-40° to +85°C

Wire/Cable Type

FFC/FPC

Electrical

Current - Maximum per Contact

1.0A

Voltage - Maximum

125V

Material Info

Reference - Drawing Numbers

Packaging Specification

SPK-52610-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52610 Series

Mates With

Molex Premo-Flex FFC. Be sure to match like plating

This document was generated on 10/29/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION