

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0747220001](#)  
**Status:** **Active**  
**Overview:** SFP+ and SFP Interconnect Solutions  
**Description:** 1-by-2 Small Form-factor Pluggable (SFP) Ganged Cage, Elastomeric Gasket, Press-fit

**Documents:**

[3D Model](#) [Test Summary TS-74722-0001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                |  |
|----------------|--|
| Product Family | I/O Connectors   |
| Series         | 74722  |
| Application    | Module-to-Board  |
| Comments       | PCB Thickness: 1.60mm Single Sided Use & 3.00mm Belly-to-belly Use 2 Ports |
| Component Type | Cage Assembly  |
| Overview       | <a href="#">SFP+ and SFP Interconnect Solutions</a>                        |
| Product Name   | SFP  |
| Type           | N/A  |
| UPC            | 822348095773   |

**Physical**

|                                |                              |
|--------------------------------|------------------------------|
| Circuits (Loaded)              | N/A                          |
| Keying to Mating Part          | None                         |
| Lock to Mating Part            | Yes                          |
| Material - Plating Mating      | N/A                          |
| Net Weight                     | 9.000/g                      |
| Orientation                    | Right Angle                  |
| PC Tail Length                 | 3.05mm                       |
| PCB Retention                  | Yes                          |
| PCB Thickness - Recommended    | 1.57mm, 3.00mm               |
| Packaging Type                 | Tray                         |
| Panel Mount                    | No                           |
| Pitch - Mating Interface       | N/A                          |
| Polarized to Mating Part       | Yes                          |
| Polarized to PCB               | Yes                          |
| Ports                          | 2                            |
| Surface Mount Compatible (SMC) | No                           |
| Temperature Range - Operating  | -55°C to +105°C              |
| Termination Interface: Style   | Through Hole - Compliant Pin |

**Electrical**

|                               |     |
|-------------------------------|-----|
| Current - Maximum per Contact | N/A |
| Grounding to Panel            | N/A |
| Shielded                      | Yes |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
| Process Temperature max. C  | 070 |

**Material Info**

**Reference - Drawing Numbers**

|               |                            |
|---------------|----------------------------|
| Sales Drawing | SD-73927-250, SD-74722-001 |
| Test Summary  | TS-74722-0001              |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2014 December 17): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[74722 Series](#)

This document was generated on 06/29/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**