

## 13A 2 Gang Switched Socket IP55 Model PL15868

RoHS  
Compliant

Specification	
Description	Material
Socket faceplate	PC
Spring	Steel
Shutter	PA
E-Conductor	Brass
L-Conductor	Brass
N-Conductor	Brass
Socket Base	PC
Screw	Steel
Box Cover	PC
Small Waterproof Loop	Silicone
Back Box	PC
Transparent Window	PVC

Voltage	Current Rating	Standard
250V AC	13A	BS1363-2

### Conditions of use

1. Ambient temperature in the range  $-5^{\circ}\text{C}$  to  $+40^{\circ}\text{C}$ , the average value over 24 hours not exceeding  $25^{\circ}\text{C}$ .
2. Situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits specified in 1.
3. Altitude not exceeding 2000 metres above sea level;



**Important Notice** : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.