


# PRODUCT DATASHEET

## HB 95 W 4000 K 90DEG IP65 BK

HIGH BAY Gen 2 | High-bay luminaires up to 135 lm/W



---

### AREAS OF APPLICATION

- Replacement for high bay luminaires with mercury vapor or metal halide lamps
- Warehouses
- Logistics halls
- Industry
- Indoor and outdoor
- High ceiling (e.g. in shopping malls, airports, commercial buildings, lobbies)

---

### PRODUCT BENEFITS

- High luminous efficacy
- Exclusive LEDVANCE design
- Energy savings of up to 60 % compared to conventional high bay luminaires
- 5 years guarantee
- Optimized weight and size due to compact design

---

### PRODUCT FEATURES

- Luminous efficacy: up to 135 lm/W
- Type of protection: IP65
- Available with beam angle: 70°, 90°, 110°



**TECHNICAL DATA**

Electrical data

Nominal wattage	95.00 W
Operating mode	Electronic control gear (ECG)
Nominal voltage	100...240 V
Power factor $\lambda$	$\geq 0.95$
Mains frequency	50/60 Hz

Luminaire control gear data

Ouput current	400 mA
---------------	--------


Photometrical data

Color temperature	4000 K
Luminous efficacy	135 lm/W
Luminous flux	13000 lm
Standard deviation of color matching	$\leq 5$ sdc <sub>m</sub>
Light color (designation)	Cool White
Color rendering index Ra	>80

Light technical data

Beam angle	90 °
------------	------

Dimensions & weight



Diameter	285.0 mm
Height	129.5 mm
Product weight	3135.00 g
Cable length	1500 mm

Colors & materials

<b>Body material</b>	Aluminum
<b>Housing color</b>	Black
<b>Product color</b>	Black

#### Temperatures & operating conditions

<b>Ambient temperature range</b>	-30...50 °C
----------------------------------	-------------

#### Lifespan

<b>Lifespan L70 at 25 °C</b>	50000 h
<b>Lifespan L80 at 25 °C</b>	35000 h
<b>Lifespan L90 at 25 °C</b>	20000 h
<b>Number of switching cycles</b>	50000

#### Additional product data

<b>Mounting type</b>	Suspended/Surface
<b>Mounting location</b>	Ceiling



#### Capabilities

<b>Dimmable</b>	No
<b>Type of connection</b>	Cable, 3-pole
<b>LED module replaceable</b>	Not replaceable

#### Certificates & standards

<b>Protection class IK (shock resistance)</b>	IK08
<b>Glow Wire Test according to IEC 695-2-1</b>	650 °C
<b>Photobiological safety group</b>	RG 0
<b>Protection class</b>	I
<b>Type of protection</b>	IP65
<b>Standards</b>	CE/CB/TÜV SÜD

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Mounting hook and brackets included

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075074330	HB 95 W 4000 K 90DEG IP65 BK	Shipping carton box 1	334 mm x 334 mm x 188 mm	20.97 dm <sup>3</sup>	4034.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see  
 ▶ [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.