

# PRODUCT DATASHEET HB 165 W 4000 K 70DEG BK IP65

HIGH BAY Gen 2 | High-bay luminaires up to 135 lm/W



#### **AREAS OF APPLICATION**

- Replacement for high bay luminaires with mercury vapor or metal halide lamps
- Warehouses
- Logistics halls
- Industry
- Indoor and outdoor
- High ceiling (e.g. in shopping malls, airports, commercial buildings, lobbies)

#### **PRODUCT BENEFITS**

- High luminous efficacy
- Exclusive LEDVANCE design
- Energy savings of up to 60 % compared to conventional high bay luminaires
- 5 years guarantee
- Optimized weight and size due to compact design

#### **PRODUCT FEATURES**

- Luminous efficacy: up to 135 lm/W
- Type of protection: IP65
- Available with beam angle: 70°, 90°, 110°



## **TECHNICAL DATA**

## Electrical data

Nominal wattage 165.00 W		
Operating mode Electronic control gear (ECG)		
Nominal voltage	100240 V	
Power factor λ	≥0.95	
Mains frequency	50/60 Hz	


#### Photometrical data

Color temperature	4000 K	
Luminous efficacy	135 lm/W	
Luminous flux	22000 lm	
Standard deviation of color matching	≤5 sdcm	
Light color (designation)	Cool White	
Color rendering index Ra	>80	

## Light technical data

Beam angle	70 °

## Dimensions & weight



Diameter	376.0 mm
Height	139.0 mm
Product weight	4365.00 g
Cable length	1500 mm

## Colors & materials

Body material	Aluminum
Housing color	Black
Product color	Black

## Temperatures & operating conditions

Ambient temperature range	-3050 °C
Lifespan	
Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	35000 h
Lifespan L90 at 25 °C	20000 h
Number of switching cycles	50000

## Additional product data

Mounting type	Suspended/Surface	
Mounting location	Ceiling	


# Capabilities


Dimmable	No	
Type of connection	Cable, 3-pole	
LED module replaceable	Not replaceable	

#### Certificates & standards

Protection class IK (shock resistance)	IK08	
Photobiological safety group	RG 0	
Protection class	1	
Type of protection	IP65	
Standards	CE/CB/TÜV SÜD/RoHS	

#### **Light Distribution**





LDC typ cone LDC typ polar

## **EQUIPMENT / ACCESSORIES**

- Mounting hook and brackets included

## **LOGISTICAL DATA**

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075074361	HB 165 W 4000 K 70DEG BK IP65	Shipping carton box 1	409 mm x 409 mm x 198 mm	33.12 dm³	5761.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### **REFERENCES / LINKS**

For Guarantee see

www.ledvance.com/guarantee

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.