

# PRODUCT DATASHEET

## P CLAS B 25 CL 2.5 W/2700 K B22d

PARATHOM Retrofit CLASSIC B | LED lamps, classic mini-candle shape



---

### AREAS OF APPLICATION

- Perfect for decorative installations
- Domestic applications
- General illumination
- Outdoor use in outdoor luminaires only (minimum IP65)

---

### PRODUCT BENEFITS

- Lamps with innovative LED "filament" technology
- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Lower thermal output (compared with the standard reference product)

---

### PRODUCT FEATURES

- Professional LED lamps for line voltage
- Beam angle: up to 300°
- Not dimmable
- Base: E14
- Mercury-free lamps
- Lifetime: up to 15,000 h



## TECHNICAL DATA

### Electrical data

Rated wattage	2.50 W
Nominal wattage	2.50 W
Nominal voltage	220...240 V
Operating frequency	50...60 Hz
Power factor $\lambda$	> 0.40
Claimed equiv. conventional lamp power	25 W


### Photometrical data

Nominal luminous flux	250 lm
Rated luminous flux	250 lm
Rated color temperature	2700 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	250 lm
Color rendering index Ra	$\geq 80$
Standard deviation of color matching	$\leq 6$ sdc <sub>m</sub>

### Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

### Dimensions & weight



Overall length	92.0 mm
Diameter	35.0 mm
Outer bulb	B35
Length	92.0 mm

## Temperatures &amp; operating conditions

Maximum temperature at tc test point	65 °C
--------------------------------------	-------

## Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

## Additional product data

Base (standard designation)	B22d
Mercury content	0.0 mg
Mercury-free	Yes
Show WEEE picto	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

## Capabilities

Dimmable	No
----------	----

## Certificates &amp; standards

Energy efficiency class	A++
Energy efficiency class	A++
Energy consumption	3 kWh/1000h

## Country-specific categorizations

Order reference	LEDPCLB25 2,5W/
-----------------	-----------------

## LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075061750	P CLAS B 25 CL 2.5 W/2700 K B22d	Shipping carton box 10	205 mm x 87 mm x 123 mm	2.19 dm <sup>3</sup>	348.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.