

Product Data Sheet



R6J100A3B

Reinforced
Class J Fuse Holder
100 Amps, 600 Volts AC/DC



Wire Range:

- #2/0 - #14 AWG Copper
- #2/0 - #12 AWG Aluminum

Holds fuse size 1 1/8" diameter X 4 5/8"

Commonly used fuses in this holder: A4J, AJT, JKS, JLS, JTD, JTD_ID, LPJ

[See table below for wire sizes.](#)

Electrical Ratings:

- 61 - 100A max (amperage rating based on maximum fuse rating for that physical size)
- 600 Volts AC/DC
- Approved for 200,000 Amp Withstand Rating

Mechanical Ratings:

- Insulator base temperature rating: -40°C/F to 150°C (302°F) UL RTI
- Flammability rating of insulator base: UL 94 V-0
 - Use outside these ratings needs to be judged in the end-use application.

Materials:

- Fuse Clip: Copper alloy, tin plated
- Box Connector: High conductivity aluminum, tin plated
- Reinforcing Spring: Steel, zinc plated
- Insulator base: Phenolic
- Terminal set screws: Aluminum, tin plated
- Connector mounting screws: Steel, zinc plated

Agency Approvals:


- UL Listed, Fuseholder standards UL 4248-1 and UL 4248-8.
- UL File No. IZLT.E35113
- CSA Certified, CSA C22.2 No. 39 – M1987, File No. LR21455
- CE compliant to IEC 60947-1
- RoHS Compliant

Wire Approvals:

Wire Size	Torque		Copper Wire Stranding Classes - Number of Conductors		
	N-m	In. lbs	Solid	Class B	Class C
2/0 AWG	13.6	120		1	1
1/0	13.6	120		1	1
1	13.6	120		1	1
2	13.6	120		1	1
4	13.6	120		1	1
6	13.6	120		1	1
8	4.5	40		1	1
10	4.0	35	1	1	1
12	4.0	35	1	1	1
14	4.0	35	1	1	1

Aluminum stranded wire range: #2/0 – 12 AWG.

- Wire strip length – 15/16”
- Hex key needed – 3/16”
- Panel mountable: #1/4 fastener, torque to 30-40 in. lbs. (3.4 - 4.5 N-m)



WWW.MARATHONSP.COM
1-419-352-8441