

Section 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name: TS109/NC

Synonyms: EHC: 28611000001212

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC9a: Coatings and paints, thinners, paint removers.

1.3. Details of the supplier of the safety data sheet

Company name: Robnor ResinLab Ltd

31 Athena Avenue

Elgin Industrial Estate

Swindon

Wiltshire

SN2 8EJ

United Kingdom

Tel: +44(0) 1793 823741

Fax: +44(0) 1793 827033

Email: eusds@robnor.co.uk**1.4. Emergency telephone number**

Emergency tel: +44(0) 1793 823741

(office hours only)

Section 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification under CLP: Flam. Liq. 3: H226; Asp. Tox. 1: H304; STOT SE 3: H336; Aquatic Chronic 2: H411; -: EUH066

Most important adverse effects: Flammable liquid and vapour. May be fatal if swallowed and enters airways. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects. Repeated exposure may cause skin dryness or cracking.

2.2. Label elements

Label elements:

Hazard statements: H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

EUH066: Repeated exposure may cause skin dryness or cracking.

SAFETY DATA SHEET

TS109/NC

Page: 2

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

GHS08: Health hazard

GHS09: Environmental



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.

No smoking.

P261: Avoid breathing vapours.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P301+P310: IF SWALLOWED: Immediately call a POISON CENTER or doctor.

P331: Do NOT induce vomiting.

P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

Rinse skin with water .

P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312: Call doctor if you feel unwell.

P273: Avoid release to the environment.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

NAPHTHA (C7-C12 HYDROCARBONS), HYDRODESULFURISED HEAVY

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-185-4	64742-82-1	-	Flam. Liq. 3: H226; Asp. Tox. 1: H304; STOT SE 3: H336; Aquatic Chronic 2: H411	70-90%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 3

water to drink immediately. If unconscious, check for breathing and apply artificial respiration if necessary. If unconscious and breathing is OK, place in the recovery position. Transfer to hospital as soon as possible.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. If conscious, ensure the casualty sits or lies down. If unconscious and breathing is OK, place in the recovery position. If unconscious, check for breathing and apply artificial respiration if necessary. If breathing becomes bubbly, have the casualty sit and provide oxygen if available. Transfer to hospital as soon as possible.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be severe pain. The eyes may water profusely.

Ingestion: May be fatal if swallowed and enters airways. There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: Aspiration hazard, do not induce vomiting if swallowed. May cause drowsiness or dizziness.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. Toxic. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Notify the police and fire brigade immediately. Eliminate all sources of ignition. Mark out the contaminated area with signs and prevent access to unauthorised personnel.
Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 4

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Clean-up should be dealt with only by qualified personnel familiar with the specific substance. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is exhaust ventilation of the area. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): PC9a: Coatings and paints, thinners, paint removers.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is exhaust ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Impermeable gloves.

Eye protection: Safety glasses with side-shields. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 5

9.1. Information on basic physical and chemical properties

State: Liquid
Colour: Colourless
Odour: Hydrocarbon
Solubility in water: Insoluble
Boiling point/range°C: 150-200
Flammability limits %: lower: 0.7
upper: 7.0
Flash point°C: 40
Relative density: 0.785

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

NAPHTHA (C7-C12 HYDROCARBONS), HYDRODESULFURISED HEAVY

DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg
VAPOURS	RAT	4H LC50	>7.63	mg/l

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 6

Relevant hazards for product:

Hazard	Route	Basis
STOT-single exposure	-	Hazardous: calculated
Aspiration hazard	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be severe pain. The eyes may water profusely.

Ingestion: May be fatal if swallowed and enters airways. There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: Aspiration hazard, do not induce vomiting if swallowed. May cause drowsiness or dizziness.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

NAPHTHA (C7-C12 HYDROCARBONS), HYDRODESULFURISED HEAVY

Daphnia magna	48H EC50	4.5	mg/l
FISH	96H LC50	8.2	mg/l
GREEN ALGA (Selenastrum capricornutum)	72H ErC50	3.1	mg/l

12.2. Persistence and degradability

Persistence and degradability: Readily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Insoluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 7

Waste code number: 14 06 02

Disposal of packaging: Arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1300

14.2. UN proper shipping name

Shipping name: TURPENTINE SUBSTITUTE

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: Marine pollutant(s) - NAPHTHA (C7-C12 HYDROCARBONS), HYDRODESULFURISED HEAVY ;

Tunnel code: D/E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

[cont...]

SAFETY DATA SHEET

TS109/NC

Page: 8

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.