

## EZYPAT PLUS

Manual PAT Tester with auto sequences and 230/110V run test.



### PRODUCT DATA SHEET

- Battery operated
- Automatic test sequences
- Appliance status pre-check
- PASS / FAIL – Green / Red screens
- Fast continuity test
- 5 second continuity test
- 250V Insulation
- 500V Insulation
- Substitute leakage test
- 110V & 230V run / leakage test
- Extension lead test with L-N ins. test
- Test lead nulling
- Backlight

### ACCESSORIES

- Mains leads
- Earth lead with probe and croc clip
- Extension lead adapter
- Carry bag with strap
- Quickstart manual
- End of line Cal Cert

### OPTIONAL

- Pass & Fail labels
- PATLOG1 PAT testing record log book
- Calibration Certificate
- KEWPAT APP

### APPLICABLE STANDARDS

Safety	IEC/EN61010-1 CAT II 300V-instrument IEC/EN61010-2-030 IEC/EN61010-031 CAT III 600V
EMC	EN61326-1, 2-2
Possible number of measurements where battery voltage is within the effective range (measuring every 30 sec)	Approx. 1400 times (CLI Rpe: 0 Ω, Rins: 1.1 MΩ)

### SPECIFICATIONS

#### PROTECTIVE CONDUCTOR RESISTANCE TEST

Measuring range	0.00 - 20.00 Ω (NULL value inc)*
Over-range indication	> 20.00 Ω
Resolution	0.01Ω
Open-circuit voltage	5 V ±0.4 V DC
Measuring current	200 mA DC (nominal value)
Accuracy	±3%rdg ±5dgt

\* Resistances exceeding 3 Ω cannot be cancelled by NULL function.

#### MAINS VOLTAGE

Display range	30 - 270 V
Hi/ Lo indication	< 30 V: No voltage indication > 270 V: 270 V
Resolution & Accuracy	1 V ±3%rdg ±5dgt

#### INSULATION

Rated voltage	250V	500V
Measuring range	0.00 - 20.00 MΩ	
Over-range indication	> 20.00 MΩ	
Resolution	0.01 MΩ	
No-load voltage	250 V DC +20%, -0%	500 V DC +20%, -0%
Short-circuit current	1.5 mA DC or less	
Rated current	1 -1.2 mA with a load of 0.25 MΩ	1 to 1.2 mA with a load of 0.5 MΩ
Accuracy	±2%rdg ±3dgt	

#### SUBSTITUTE LEAKAGE

Measuring range	0.10 - 12.00 mA rms
Over-range indication	> 12.00 mA
Resolution	0.01mA
Open-circuit voltage/ Freq.	30 V ±5 V rms / 50 Hz ±5%
Measuring current	1.2 mA AC ±0.5 mA (when measuring 12.00 mA)
Accuracy	±3%rdg ±5dgt

#### INSULATION TEST BETWEEN L-N

Open-circuit voltage	4.5 V ±0.5 V DC
Criteria of judgement	100 kΩ ±20 kΩ or less: LCD shows "<0.10 MΩ" and the measurement is halted.

#### RUN LEAKAGE

Item	Load current	Leakage current
Mains voltage range	100 - 253 V / 50 Hz	
Measuring range	0.10 - 13.00 A rms	0.10 - 20.00 mA rms
Display range	0.00 - 13.00 A	0.00 - 20.00 mA
Over-range indication	> 13.00 A	> 20.00 mA
Resolution	0.01A	0.01mA
Accuracy	±10%rdg ±5dgt	±3%rdg ±5dvt
Max. rating	3 kVA max. / 15 sec. cont.	