Product data sheet







Product description Contacts: 8, Connecting cable 10m, male cable connector M12x1 - RJ45-male connector, shielded, IP67

Area M12-D, M12-X Series 876 X-coding

Order number 79 9723 100 08







Technical data

General values

Connector design Connector locking system Termination Wire gauge (AWG) Upper limit temperature Lower limit temperature connecting cord bolted moulded on cable 4x2xAWG26 85 °C -40 °C

Cable data

Sheath material

Single-lead insulation
Single-lead structure
Cable diameter
Conductor resistance
Temperature range, moving cable, °C from
Temperature range, fixed cable, °C from
Temperature range, fixed cable, °C to
Bending radius, fixed cable
Approval 1

PUR
PE
8 x 0,14
6.2
14,5Ω/100 m
-10
60
-40
85
≥ 50 mm
UL listed

Electrical values

Rated current (40 °C) 50V AC, 60V DC V Rated voltage Pollution degree Overvoltage category Ш Insulating material group Ш Volume resistivity \leq 15 m Ω Insulation resistance >10^8Ω EMC compliance shielded Degree of protection > 100 Mating cycles Mechanical operation

Material

Contact material Contact plating Contact body material Housing material CuZn (brass) Au (gold) PA PUR

Product data sheet



Automation technology - data transmission and power supply

Product description Contacts: 8, Connecting cable 10m, male cable connector M12x1 - RJ45-male connector, shielded, IP67

Area M12-D, M12-X Series 876 X-coding

Order number **79 9723 100 08**

Security notices

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.

Connectors with degree of protection IP 67 and IP 68 are not suitable for use under water. When used outdoors, the connectors must be separately protected against corrosion. For further information about IP degrees of protection refer to 'Technical support' in the Download Centre.

To lock the cable connector to the equipment connector, the threaded ring is tightened until it is 'finger-tight' (approx. 50 cNm).

