



Standard Battery Charger RRC-SCC-EZP for Varta EasyPack batteries S, L, XL and PLUS

Features:

- 5W single bay charger
- For the standard Varta EasyPack batteries S, L, XL and PLUS
- Simple operation – Plug and Play
- External wall plug power supply for worldwide use



Applications:

Charging station for VARTA EasyPack battery packs for mobile devices used in industry and customer areas

Specification RRC-SCC-EZP

Input		Output	
Voltage	5V nom.	Voltage	4.2VDC
Current	1000mA nom.	Volt. tolerance	±1 % max.
Power	5W	Current max.	1A max. for EZPack L, XL, PLUS 0.5A max. for the EZPack S
		Protection	Short circuit Battery over/under temperature Charger over temperature Charge timer

Environmental		General	
Cooling	convection cooled	Indicator	Multi-color LED (green, red, orange)
Temperature	Operating: 0°C to 40°C Non-operating -10°C to 70°C	Battery types	EZPack S, EZPack L, EZPack XL, EZPack PLUS
Pressure & Altitude	Operating: 1060hPa to 795hPa -382m to 2000m Non-operating: 1060hPa to 572hPa -382m to 4570m	Energy Efficiency	CEC, DoE
Humidity	5% to 95% r.H., non-condensing	Green procurement	RoHS 2011/65/EU WEEE 2012/19/EU

LED Indications	
Orange light	The inserted battery is currently being charged.
Green light	The battery is charged and can be removed for use.
Red blinking	Battery detection phase
Red light	No battery inserted, battery over/under temperature-, charger over temperature-, battery over voltage-, battery charge timer time-out-error or input voltage too low

Charger Mechanical Details	
Housing dimensions (LxWxH)	46.7 x 101.4 x 12.5mm
Weight	26g (without power supply)

Safety & EMC			In combination with the included external power supply AC/DC	
Regulatory approvals	Europe		CE	
Electromagnetic Emissions	Europe		EN55032 class B + CISPR32 class B	
Electromagnetic Immunity	USA		FCC15 class B	
	ESD immunity		EN/IEC61000-4-2	
	Electromagnetic field immunity		EN/IEC61000-4-3	
	EFT / Burst		EN/IEC61000-4-4	
	Surge		EN/IEC61000-4-5	
	Conducted Immunity		EN/IEC61000-4-6	
	Magnetic Fields		EN/IEC61000-4-8 + -4-11	

Specification external power supply AC/DC

Input		Output	
Voltage range	100 - 240VAC	Voltage	5VDC $\pm$ 0.25V
Current	0.35A max.	Power	5W max.
Stand by power	< 0.1W @115VAC and 230 VAC	Current range	0 - 1A
		Protection	Over voltage, over current, Short circuit

Environmental		General	
Temperature	Operating: -10°C to 40°C Storage: -20°C to 70°C	Efficiency	California's Energy Efficiency Level VI
Humidity	Operating: 10% to 90% Storage: 5% to 95%	Lifetime	30000 hours min (acc. to MIL-HDBK-217F)
		Ripple & Noise	120mV max.
		Green procurement	RoHS2011/65/EU

Power Supply Mechanical Details	
Standard output connector	USB Micro 5pin
Standard input connector	Wall mount type EU, USA, AUS and UK
Housing dimensions (LxWxH)	54.8 x 29.45 x 44.9mm (without wall-mount plug)
Weight	45g $\pm$ 10g

Safety & EMC & Approvals		
Approvals	Europe	CE
	International	CB
	USA/Canada	cETLus
	Australia	SAA

Germany/Headquarters

RRC power solutions GmbH
 Technologiepark 1
 D-66424 Homburg / Saar

Tel.: +49 6841 98090
 Fax: +49 6841 9809280
 Email: sales@rrc-ps.de
 Web: www.rrc-ps.de

USA

RRC power solutions Inc.
 18340 Yorba Linda Blvd.,
 Suite 107-437
 Yorba Linda, CA 92886-4104

Tel.: +1 714 777 3604
 Fax: +1 714 777 3658
 Email: usa@rrc-ps.com
 Web: www.rrc-ps.com

Hong Kong

RRC power solutions Ltd.
 S-V,6/F, Valiant Industrial Centre
 2-12 Au Pui Wan Street
 Fo Tan, N.T., Hong Kong

Tel.: +852 2376 0106
 Fax: +852 2375 0107
 Email: hkrrc@rrc-ps.cn
 Web: www.rrc-ps.com

China

RRC power solutions Ltd.
 Room 520, Yuanlin Building,
 Aiguo Road No. 3066,
 Luohu District,
 Shenzhen 518021

Tel.: +86 755 8374 1908
 Fax: +86 755 8374 1861
 Email: hkrrc@rrc-ps.cn
 Web: www.rrc-ps.com