




Notes: 1.Material:TPR UL94 HB(Feet Body) PA6 UL94 V2(Rivet Body) POM UL94 HB(Rivet Pin) 2.RoHS Compliant; 3.Hole:Ø5.0-5.1mm;Panel Thickness:1.0-2.3mm.		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS. SURFACE FINISH: TOLERANCES: L≤4 = ±0.1 4<L≤15 = ±0.2 15<L≤50 = ±0.3 50<L≤100 = ±0.4	MATERIAL		TITLE							
			SEE NOTES									
			HEAT TREATMENT		SOFT FAST FOOT							
			N/A									
			DRAWN				DATE					
CHK'D		08/08/2013										
APPV'D												
DESIGN RIGHT. TR FASTENINGS LTD, 2003 UNDER NO CIRCUMSTANCES MUST THIS DRAWING BE COPIED OR DISCLOSED, WITHOUT FIRST OBTAINING WRITTEN AUTHORITY.		CUSTOMER PART NO.		FINISH		DWG NO.		A3				
				Black		TRFF-004						
1	2	3	4	PROJECTION							SHEET 1 OF 1	