

4mm Insulated Binding Post w/ 2mm Drilling & M6 Threaded Stud & Hex Nuts



Specifications

Connector Type	: 4mm Insulated Binding Post
Connector Mounting	: Panel Mount
Termination Type	: 2mm Turret & M6 Threaded Stud & Hex Nuts
Voltage Rating	: ≤30VAC / ≤60VDC
Current Rating	: 36A
Contact Material	: Brass, Nickel Plating
Insulators Material	: POM
Connector Colour	: Red, Blue and Black

Part Number Table

Description	Part Number
4mm Insulated Binding Post w/ 2mm Turret & M6 Threaded Stud & Hex Nut, 30V AC/60V DC, 36A, Red	76-1674
4mm Insulated Binding Post w/ 2mm Turret & M6 Threaded Stud & Hex Nut, 30V AC/60V DC, 36A, Blue	76-1476
4mm Insulated Binding Post w/ 2mm Turret & M6 Threaded Stud & Hex Nut, 30V AC/60V DC, 36A, Black	76-1672

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

