

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1451300500](#)  
**Status:** **Active**  
**Overview:** Nano-Fit Power Connectors  
**Description:** Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Single Row, 75.00mm Length, 5 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">145130</a>
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	No
Overview	<a href="#">Nano-Fit Power Connectors</a>
Product Literature Order No	987651-6143
Product Name	Nano-Fit OTS
UPC	191130118892

**Physical**

Cable Length	75.00mm
Circuits (Loaded)	5
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	5.610/g
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm
Wire Size AWG	20
Wire/Cable Type	UL 1061


**Electrical**

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	4000095320-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[145130 Series](#)

**Mates With**

Nano-Fit Headers [105309](#) , [105311](#) , [105321](#)