

This document was generated on 10/24/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430451219

Status: Active

Overview: Micro-Fit 3.0 Connector System Product Family

Description: Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Dual Row, 12 Circuits, with Solder Tab,

Gold, Glow-Wire Capable, Black

Documents:

3D ModelProduct Specification TS-43045-002-001 (PDF)Drawing (PDF)Product Specification TS-46235-001-001 (PDF)Product Specification PS-43045 (PDF)Packaging Specification PK-70873-05XX-002 (PDF)

Product Specification PS-43045-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification TS-43045-001-001 (PDF)

Product Literature (PDF)

Agency Certification

CSA LR19980 UL E29179

General

Product Family PCB Headers

Series <u>43045</u>

Application Power, Wire-to-Board Comments """"""High Temperature|Squ

"""""High Temperature|Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product enduse standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher


performance is required, please contact Molex for possible product options."""""""

Overview Micro-Fit 3.0 Connector System Product Family

Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0
UPC 800754373319

Physical

Breakaway No Circuits (Loaded) 12 Circuits (maximum) 12 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Capable Yes Mated Height 17.64mm Material - Metal **Brass** Material - Plating Mating Gold



EU ELV

Not Relevant

EU RoHS China RoHS

Compliant

REACH SVHC
Not Contained Per -

ED/61/2018 (27 June

2018)

Halogen-Free

<u>Status</u>

Low-HalogenFor more information, please visit <u>Contact US</u>

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

43045 Series

Mates With

Micro-Fit 3.0 Receptacle Housing <u>43025</u>

- Since the description of the second seco Material - Plating Termination Tin

Material - Resin High Temperature Thermoplastic

Net Weight1.922/gNumber of Rows2OrientationVerticalPCB LocatorYesPCB RetentionYesPCB Thickness - Recommended1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 3.00mm

Plating min - Mating 0.381µm

Polarized to PCB Yes

Shrouded Fully

Stackable No

Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

003

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-70873-05XX-002

Product Specification PS-43045, PS-43045-001, TS-43045-001,

TS-43045-002-001, TS-46235-001-001

Sales Drawing SD-43045-007-001 Symbol/Footprint Data SYM-43045-1218

This document was generated on 10/24/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION