



Item	Specifications	Typical Value	Q.C. Limit	Remark
	Frequency Range	5 ~ 2400 MHz		
	Input / Output Ports	System (1) / Subscriber (1) Port		F-Type Female Connector
	Impedance	75Ω		
Insertion Gain	5 ~ 40 MHz	-1.3 dB	≥-1.5 dB	
	40 ~ 1000 MHz	-1.3 dB	≥-1.5 dB	
	1000 ~ 1750 MHz	-1.8 dB	≥-2.0 dB	
	1750 ~ 2400 MHz	-2.8 dB	≥-3.0 dB	
Return Loss	5 ~ 40 MHz	10 dB	≥8 dB	
	40 ~ 750 MHz	15 dB	≥14 dB	
	750 ~ 1000 MHz	15 dB	≥13 dB	
	1000 ~ 1750 MHz	14 dB	≥12 dB	
	1750 ~ 2400 MHz	12 dB	≥9 dB	
	1750 ~ 2400 MHz	12 dB	≥9 dB	
	Surge Protection	2kV DC, 3s, 1mA		No Spark or Breakdown

### Part Number Table

Description	Part Number
Isolation Transformer / Ground Loop Isolator	4170

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell Limited 2016.