

# DisplayPort to VGA Adapter Cable



## Features

- DisplayPort 1.1a compliant receiver offering 5.4 Gbps bandwidth over 2 lanes
- Integrated triple 10-bit, 162 MHz video DAC for analog VGA signal output
- Supports up to 1080p, 1920 x 1200 reduced blanking video resolution
- EDID pass-through from PC source to display
- Spread Spectrum (de-spreading) for EMI reduction
- Automatic sink detection
- Low power standby mode operation initiated based on sink detection status
- Powered from DisplayPort source
- 3.3V IO, 1.2V Core
- Low power operation – Active 400mW, standby mode 15mW

Note: For few display cards, the image would not appear until the PC enters into Windows from DOS at the time of restarting.

## Specifications

### Signal Inputs/Output

Maximum Single Link Range : 1920×1200, 1080P

### Video format supported

VGA : Max to 1920×1200

### Operating Frequency

Vertical Frequency Range : 50/60Hz

Video Amplifier Bandwidth : 162MHz

### Mechanical

Size (L×W×H) : 41.9mm × 37mm × 14.5mm

Weight (Net) : 22g

### Environmental

Operating Temperature : 0°C to +45°C

Operating Humidity : 10% to 85% RH (no condensation)

Storage Temperature : -10°C to +80°C

Storage Humidity : 5% to 90 % RH (no condensation)

Power Requirement : No

## Connection Diagram



## Part Number Table

Description	Part Number
DisplayPort to VGA Adapter Cable	DPV-15CM