

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0438790032](#)
Status: **Active**
Overview: [Mini-Fit BMI Connectors](#)
Description: Mini-Fit BMI Header Compliant Pin Interface, Dual Row, Vertical, 24 Circuits, Tin (Sn) Plating

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-43879-001-001 \(PDF\)](#)
[Product Specification TS-43879-001-001 \(PDF\)](#)
[Packaging Specification PK-43879-001-000 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	43879
Application	Board-to-Board, Power, Wire-to-Board
Application Tooling Part Link	62200-5800
Application Tooling Part Link	62200-9400
Comments	Square Pin Compliant Pin
Overview	Mini-Fit BMI Connectors
Product Literature Order No	USA-143
Product Name	Mini-Fit BMI
UPC	800753236509

Physical	
Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	11.048/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	6.25mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/61/2018 (27 June 2018) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[43879](#) Series

Mates With
[5557](#) Mini-Fit Jr. Receptacle Housing, [42385](#) Mini-Fit BMI Receptacle Header, Mini-Fit BMI Receptacle Housing [42474](#) , [44516](#)

Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-43879-001-000
Product Specification	PS-43879-001-001, TS-43879-001-001
Sales Drawing	SD-43879-021-000

This document was generated on 10/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION