



MPN - GRM03-KIT-TTOL-E

Description - 0201 CLASS 1 TIGHT TOLERANCE

Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Capacitance	Tolerance	Thickness (mm)	Qty
GRM0335C1HR10WA01	0603M/0201	C0G	50Vdc	0.1pF	±0.05pF	0.33max	20
GRM0335C1HR20WA01	0603M/0201	C0G	50Vdc	0.2pF	±0.05pF	0.33max	20
GRM0335C1HR30WA01	0603M/0201	C0G	50Vdc	0.3pF	±0.05pF	0.33max	20
GRM0335C1HR40WA01	0603M/0201	C0G	50Vdc	0.4pF	±0.05pF	0.33max	20
GRM0335C1HR50WA01	0603M/0201	C0G	50Vdc	0.5pF	±0.05pF	0.33max	20
GRM0335C1HR60WA01	0603M/0201	C0G	50Vdc	0.6pF	±0.05pF	0.33max	20
GRM0335C1HR70WA01	0603M/0201	C0G	50Vdc	0.7pF	±0.05pF	0.33max	20
GRM0335C1HR80WA01	0603M/0201	C0G	50Vdc	0.8pF	±0.05pF	0.33max	20
GRM0335C1HR90WA01	0603M/0201	C0G	50Vdc	0.9pF	±0.05pF	0.33max	20
GRM0335C1H1R0BA01	0603M/0201	C0G	50Vdc	1.0pF	±0.1pF	0.33max	20
GRM0335C1H1R1BA01	0603M/0201	C0G	50Vdc	1.1pF	±0.1pF	0.33max	20
GRM0335C1H1R2BA01	0603M/0201	C0G	50Vdc	1.2pF	±0.1pF	0.33max	20
GRM0335C1H1R3BA01	0603M/0201	C0G	50Vdc	1.3pF	±0.1pF	0.33max	20
GRM0335C1H1R4BA01	0603M/0201	C0G	50Vdc	1.4pF	±0.1pF	0.33max	20
GRM0335C1H1R5BA01	0603M/0201	C0G	50Vdc	1.5pF	±0.1pF	0.33max	20
GRM0335C1H1R6BA01	0603M/0201	C0G	50Vdc	1.6pF	±0.1pF	0.33max	20
GRM0335C1H1R7BA01	0603M/0201	C0G	50Vdc	1.7pF	±0.1pF	0.33max	20
GRM0335C1H1R8BA01	0603M/0201	C0G	50Vdc	1.8pF	±0.1pF	0.33max	20
GRM0335C1H1R9BA01	0603M/0201	C0G	50Vdc	1.9pF	±0.1pF	0.33max	20
GRM0335C1H2R0BA01	0603M/0201	C0G	50Vdc	2.0pF	±0.1pF	0.33max	20
GRM0335C1H2R1BA01	0603M/0201	C0G	50Vdc	2.1pF	±0.1pF	0.33max	20
GRM0335C1H2R2BA01	0603M/0201	C0G	50Vdc	2.2pF	±0.1pF	0.33max	20
GRM0335C1H2R3BA01	0603M/0201	C0G	50Vdc	2.3pF	±0.1pF	0.33max	20
GRM0335C1H2R4BA01	0603M/0201	C0G	50Vdc	2.4pF	±0.1pF	0.33max	20
GRM0335C1H2R5BA01	0603M/0201	C0G	50Vdc	2.5pF	±0.1pF	0.33max	20
GRM0335C1H2R6BA01	0603M/0201	C0G	50Vdc	2.6pF	±0.1pF	0.33max	20
GRM0335C1H2R7BA01	0603M/0201	C0G	50Vdc	2.7pF	±0.1pF	0.33max	20
GRM0335C1H2R8BA01	0603M/0201	C0G	50Vdc	2.8pF	±0.1pF	0.33max	20
GRM0335C1H2R9BA01	0603M/0201	C0G	50Vdc	2.9pF	±0.1pF	0.33max	20
GRM0335C1H3R0BA01	0603M/0201	C0G	50Vdc	3.0pF	±0.1pF	0.33max	20
GRM0335C1H3R6BA01	0603M/0201	C0G	50Vdc	3.6pF	±0.1pF	0.33max	20

GRM0335C1H3R9BA01	0603M/0201	C0G	50Vdc	3.9pF	±0.1pF	0.33max	20
GRM0335C1H4R3BA01	0603M/0201	C0G	50Vdc	4.3pF	±0.1pF	0.33max	20
GRM0335C1H4R7BA01	0603M/0201	C0G	50Vdc	4.7pF	±0.1pF	0.33max	20
GRM0335C1H5R1BA01	0603M/0201	C0G	50Vdc	5.1pF	±0.1pF	0.33max	20
GRM0335C1H5R6BA01	0603M/0201	C0G	50Vdc	5.6pF	±0.1pF	0.33max	20
GRM0335C1H6R2BA01	0603M/0201	C0G	50Vdc	6.2pF	±0.1pF	0.33max	20
GRM0335C1H6R8BA01	0603M/0201	C0G	50Vdc	6.8pF	±0.1pF	0.33max	20
GRM0335C1H7R5BA01	0603M/0201	C0G	50Vdc	7.5pF	±0.1pF	0.33max	20
GRM0335C1H8R2BA01	0603M/0201	C0G	50Vdc	8.2pF	±0.1pF	0.33max	20
GRM0335C1H9R1BA01	0603M/0201	C0G	50Vdc	9.1pF	±0.1pF	0.33max	20
GRM0335C1H100GA01	0603M/0201	C0G	50Vdc	10pF	±2%	0.33max	20
GRM0335C1H120GA01	0603M/0201	C0G	50Vdc	12pF	±2%	0.33max	20
GRM0335C1H150GA01	0603M/0201	C0G	50Vdc	15pF	±2%	0.33max	20
GRM0335C1H180GA01	0603M/0201	C0G	50Vdc	18pF	±2%	0.33max	20
GRM0335C1H220GA01	0603M/0201	C0G	50Vdc	22pF	±2%	0.33max	20
GRM0335C1H270GA01	0603M/0201	C0G	50Vdc	27pF	±2%	0.33max	20
GRM0335C1H330GA01	0603M/0201	C0G	50Vdc	33pF	±2%	0.33max	20
GRM0335C1H390GA01	0603M/0201	C0G	50Vdc	39pF	±2%	0.33max	20
GRM0335C1H470GA01	0603M/0201	C0G	50Vdc	47pF	±2%	0.33max	20
GRM0335C1H560GA01	0603M/0201	C0G	50Vdc	56pF	±2%	0.33max	20
GRM0335C1H680GA01	0603M/0201	C0G	50Vdc	68pF	±2%	0.33max	20
GRM0335C1H820GA01	0603M/0201	C0G	50Vdc	82pF	±2%	0.33max	20
GRM0335C1H101GA01	0603M/0201	C0G	50Vdc	100pF	±2%	0.33max	100
GRM0335C1H121GA01	0603M/0201	C0G	50Vdc	120pF	±2%	0.33max	20
GRM0335C1H151GA01	0603M/0201	C0G	50Vdc	150pF	±2%	0.33max	20
GRM0335C1H181GA01	0603M/0201	C0G	50Vdc	180pF	±2%	0.33max	20
GRM0335C1H221GA01	0603M/0201	C0G	50Vdc	220pF	±2%	0.33max	20
GRM0335C1E271GA01	0603M/0201	C0G	25Vdc	270pF	±2%	0.33max	20
GRM0335C1E331GA01	0603M/0201	C0G	25Vdc	330pF	±2%	0.33max	20
GRM0335C1E391GA01	0603M/0201	C0G	25Vdc	390pF	±2%	0.33max	20
GRM0335C1E471GA01	0603M/0201	C0G	25Vdc	470pF	±2%	0.33max	20
GRM0335C1E561GA01	0603M/0201	C0G	25Vdc	560pF	±2%	0.33max	20
GRM0335C1E681GA01	0603M/0201	C0G	25Vdc	680pF	±2%	0.33max	20
GRM0335C1E821GA01	0603M/0201	C0G	25Vdc	820pF	±2%	0.33max	20
GRM0335C1E102GA01	0603M/0201	C0G	25Vdc	1000pF	±2%	0.33max	20