

Specification Sheet

Part Number: 156-00862



Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC5B, 1–3 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number	156-00862
Type	T50ROSEC5B
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.•Edge Clip provides low insertion force and high extraction force ideal for assembly environments.•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.•Cable tie is outside serrated to reduce bundle chafing.
Quantity Per	bag

Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description	Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC5B, 1-3 mm Panel, 50lb, PA66HS, Black, 500/pkg
Global Part Name	T50ROSEC5B-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	202.0
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Identification Plate Position	none
Releasable Closure	No
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	.05
Height H (Metric)	1.30
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	500

Package Quantity (Metric)

500

Customs Number

3926909987

Weight (Metric)

4.5