

Specification Sheet

Part Number: 156-00588



Cable Tie & Edge Clip, 8.0" Long, EC4B, 1–3 mm Panel, 50lb, PA66UV/PA66HIRHSUV, Black, 100/pkg

Article Number	156-00588
Type	T50REC4B
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.• Edge Clip provides low insertion force and high extraction force ideal for assembly environments.• Two piece assembly allows the mount to slide along the strap ensuring proper orientation.• Cable tie is outside serrated to reduce bundle chafing.
Quantity Per	bag

Product Description

This cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description

Cable Tie & Edge Clip, 8.0" Long, EC4B, 1–3 mm Panel, 50lb, PA66UV/PA66HIRHSUV, Black, 100/pkg

Global Part Name

T50REC4B-PA66UV/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.0

Length L (Metric)

202.0

Fixation Method

EdgeClip, top, assembled, 2 piece

Identification Plate Position

none

Releasable Closure

No

Variant

Inside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

50.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.63
Height H (Metric)	16.0
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 UV-stabilized (PA66UV) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66UV PA66HIRHS
Material Cable Tie	Polyamide 6.6 UV-stabilized (PA66UV)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C) -40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	100

Package Quantity (Metric) 100

Customs Number 3926909987

Weight (Metric) 0.00294835

Weight (Imperial) 0.0065