

**PROtop
PRO COM CAN OPEN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



High-end power supplies must perform efficiently and reliably, even in challenging industrial environments. This requires high power reserves, a long service life and optimal protection against overvoltage, vibration and extreme temperature conditions.

New DCL technology gives PROtop an outstanding dynamic range. This can be used for the reliable triggering of circuit breakers or for powerful motor starts.

General ordering data

| | |
|------------|----------------------------|
| Type | PRO COM CAN OPEN |
| Order No. | 2467320000 |
| Version | |
| GTIN (EAN) | 4050118482225 |
| Qty. | 1 pc(s). |

**PROtop
PRO COM CAN OPEN**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|--------|---------|-----------------|------------|
| Width | 35 mm | Width (inches) | 1.378 inch |
| Height | 74.4 mm | Height (inches) | 2.929 inch |
| Depth | 33.6 mm | Depth (inches) | 1.323 inch |
| Weight | 36 g | Net weight | 76 g |

Temperatures

| | | | |
|-----------------------------|----------------|-----------------------------|--------|
| Operating temperature, max. | 70 °C | Operating temperature, min. | -25 °C |
| Operating temperature | -25 °C...70 °C | Storage temperature | |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

General data

| | | | |
|-----------------------|----------------|-------------------|------|
| Operating temperature | -25 °C...70 °C | Protection degree | IP20 |
| Weight | 36 g | | |

System data

| | | | |
|-----------------|----------------------------------|--------------------|----------------|
| Connection type | 2 x RJ45 plug-in connectors | Field bus protocol | CANopen |
| Interface | PROtop interconnection interface | Module type | plug-on module |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC001604 | eClass 6.2 | 27-04-90-04 |
| eClass 9.1 | 27-04-07-92 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|----------|--------------------------|
| Software | EDS File |
|----------|--------------------------|