

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050579013

Status:


Active

Overview:

SL Modular Connectors

Description:

SL Crimp Housing, Single Row, Version A, Non-polarized, 13 Circuits, Black



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-71851-001 (PDF)

Product Specification TS-70058-001-001 (PDF)

Product Specification TS-70541-001-001 (PDF)

Packaging Specification PK-70066-100 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	70066
Application	Signal, Wire-to-Board
Comments	Version A
Overview	SL Modular Connectors
Product Name	SL
UPC	800753578241
Physical	
Circuits (maximum)	13
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Resin	Polyester Alloy
Net Weight	0.093/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	3.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	70066-0012
Reference - Drawing Numbers	
Packaging Specification	PK-70066-100
Product Specification	PS-70058-001, PS-70400-001, PS-71851-001, TS-70058-001-001, TS-70541-001-001
Sales Drawing	SD-70066-0001-0024

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70066 Series

Mates With

42375 , 42377 , 70280 , 70287 , 71308 , 70543 , 70553

Use With

SL Crimp Terminal 70058 , 71851

This document was generated on 10/23/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION