

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050841065

Status:

Active

Overview:

MLX Power Connectors

Description:

2.13mm Diameter MLX Power Crimp Housing Plug, 6 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

Product Specification PS-42022-0001-001 (PDF)

Product Specification TS-42022-0001-001 (PDF)

Packaging Specification PK-42021-XX-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	42021
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 36643-0005. Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Overview	MLX Power Connectors
Product Name	MLX
UPC	800754385886
Physical	
Circuits (maximum)	6
Circuits Detail	6
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.533/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	11.0A, 20.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	4202106C
Reference - Drawing Numbers	
Packaging Specification	PK-42021-XX-001
Product Specification	PS-42022-0001-001, TS-42022-0001-001
Sales Drawing	SD-42021-**



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

42021 Series

Mates With

42002 MLX Power Connector Header,
42022 MLX Pin and Socket Receptacle,
43255 MLX Power Connector Header

Use With

MLX Crimp Terminal 36663 , 36664 , 42023 , 42024

This document was generated on 10/23/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION