

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510670500](#)
Status: **Active**
Description: 3.50mm Pitch Wire-to-Wire and Wire-to-Board Housing, Positive Lock, 5 Circuits, Natural

Documents:

3D Model	Product Specification PS-51067-008 (PDF)
Drawing (PDF)	Product Specification PS-51067-016 (PDF)
Product Specification PS-51067-001-001 (PDF)	Product Specification PS-51067-017 (PDF)
Product Specification PS-51067-002-001 (PDF)	Product Specification PS-51067-018 (PDF)
Product Specification PS-51067-003 (PDF)	Product Specification PS-51067-019-001 (PDF)
Product Specification PS-51067-004 (PDF)	Product Specification PS-51067-021-001 (PDF)
Product Specification PS-51067-005 (PDF)	Product Specification PS-51067-022-001 (PDF)
Product Specification PS-51067-006 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-51067-007 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	51067
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	N/A
UPC	800753574403


Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1068.900/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Product Specification	PS-51067-001-001, PS-51067-002-001, PS-51067-003, PS-51067-004, PS-51067-005, PS-51067-006, PS-51067-007, PS-51067-008, PS-51067-016, PS-51067-017, PS-51067-018, PS-51067-019-001, PS-51067-021-001, PS-51067-022-001
Sales Drawing	SD-51067-**00



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51067 Series](#)

Mates With

[51114](#) , [53258](#) , [53259](#) , [53265](#) , [53266](#)

Use With

[50217 Crimp Terminals](#)