

True RMS Mini Clamp Meter

TENMA™

RoHS
Compliant



Features

- 2000 Counts Display
- LCD Backlight
- Manual & Auto Ranging
- 17mm Jaw Capacity
- NCV Detector
- Data Hold
- MAX/MIN & Relative Modes
- Auto Power Off
- Low Battery Indication
- Input Protection

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

TENMA™

True RMS Mini Clamp Meter



General Characteristics

Safety Rating	: CAT II 600V, CAT III 300V
Power	: AAA 1.5V Batteries × 2
LCD Size	: 39.3mm × 26.5mm
Colour	: Orange and Grey
Weight	: 160g
Dimension	: 155mm × 60mm × 33.5mm
Standard Accessories	: Batteries & User Manual

Electrical Specifications

Parameters	Range	Best Accuracy
AC Current	2A/20A/200A	±(2.5% +5 digits)
Jaw Capacity	17mm	
Auto Power Off	Around 15 minutes	
Low Battery Indication	≤ 2.5V	

Part Number Table

Description	Part Number
True RMS Mini Clamp Meter, 17mm Jaw	72-3500

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

