# Sure Cross® DXM100-B2 Wireless Controller



# Datasheet

The DXM100-B2 Wireless Controller is an industrial wireless controller that facilitates Industrial Internet of Things (IIoT) applications. As a communications gateway, it interfaces local serial ports, local I/O ports, and local ISM radio devices to the internet using either a cellular connection or a wired Ethernet network connection.



- Sure Cross® DX80 Wireless Gateway or MultiHop radio with 900 MHz or 2.4 GHz ISM bands available
- Logic controller with action rules and ScriptBasic programming
- Cellular modem Internet connectivity
- Automation protocols include Modbus TCP, Modbus RTU, and EtherNet/IP™
- · Secure email and text Internet messaging for alarms, alerts, and data log files
- Data logging with removable SD card
- Interactive programmable user interface with LCD and LED indicators
- Universal, on-board I/O with analog and discrete I/O
- Industry standard RS-485, Ethernet, and USB communication ports
- Multiple managed power options with battery backup



#### WARNING:

- · Do not use this device for personnel protection
- Using this device for personnel protection could result in serious injury or death.
- This device does not include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A device failure or malfunction can cause either an energized (on) or deenergized (off) output condition.



#### Important:


- Never operate a 1 Watt radio without connecting an antenna
- · Operating 1 Watt radios without an antenna connected will damage the radio circuitry.
- To avoid damaging the radio circuitry, never apply power to a Sure Cross<sup>®</sup> Performance or Sure Cross MultiHop (1 Watt) radio without an antenna connected.



## Important:

- Electrostatic discharge (ESD) sensitive device
- ESD can damage the device. Damage from inappropriate handling is not covered by warranty.
- Use proper handling procedures to prevent ESD damage. Proper handling procedures include leaving devices in their anti-static packaging until ready for use; wearing anti-static wrist straps; and assembling units on a grounded, static-dissipative surface.

# Model Key for the DXM100-B2 Models



Inputs: (4) universal IN
Outputs: (4) NMOS OUT, (2) 0-10 V analog, (2) DC Latching
Power Out: (2) Adjustable 5 V to 24 V switched power,
(1) SDI switched power, and (1) 5 V courtesy power

Radio Configuration

R1

Blank = None

R1 = 900 MHz, 1 W PE5 Performance Radio (North America) R2 = 900 MHz, 1 W HE5 MultiHop Data Radio (North America)

R3 = 2.4 GHz, 65 mW PE5 Performance Radio (Worldwide) R4 = 2.4 GHz, 65 mW HE5 MultiHop Data Radio (Worldwide)

R5 = 900 MHz, 65 mW HE5L MultiHop Data Radio (Used for M-GAGE networks)

R8 = 900 MHz, Performance Radios approved for Australia/New Zealand

R9 = 900 MHz, MultiHop Radio approved for Australia/New Zealand

Some example models include, but are not limited to, the following:



Original Document 195232 Rev. E

Models	Description
DXM100-B2R1	DXM100-B2 Wireless Controller with DX80 ISM 900 MHz radio
DXM100-B2R2	DXM100-B2 Wireless Controller with DX80 ISM 900 MHz MultiHop radio
DXM100-B2R3	DXM100-B2 Wireless Controller with DX80 ISM 2.4 GHz radio
DXM100-B2R4	DXM100-B2 Wireless Controller with DX80 ISM 2.4 GHz MultiHop radio

**Cellular Communication**—Controllers accept Banner GSM and LTE modems only. Cellular modems are ordered separately as accessories under the following part numbers:

- GSM/3G (HSPA): SXI-GSM-001
- LTE-Verizon: SXI-LTE-001

# DXM100 Documentation

For more information about the DXM100 family of products, please see additional documentation and videos on the Banner website: www.bannerengineering.com.

- DXM Wireless Controller Sell Sheet, p/n 194063
- DXM100-B1 Wireless Controller Datasheet, p/n 186724
- DXM100-B2 Wireless Controller Datasheet, p/n 195232
- DXM100-Bx Wireless Controller Instruction Manual, p/n 190037
- DXM100-S1 Modbus Slave Datasheet, p/n 195454
- DXM100-S2 Modbus Slave Datasheet, p/n 195231
- DXM100-Sx Modbus Slave Instruction Manual, p/n 188231
- DXM ScriptBasic Instruction Manual, p/n 191745
- DXM Controller Configuration Quick Start, p/n 191247
- DXM Configuration Tool software (p/n b\_4447978)
- DXM Configuration Tool Instruction Manual, p/n 158447
- DXM EDS Configuration file for Allen-Bradley PLCs
- EIP Configuration File for DXM 1xx-BxR1 and R3 models (p/n 194730)
- Activating a Cellular Modem (p/n b\_4419353)
- · Additional technical notes and videos

Technical notes, configuration examples, and ScriptBasic program examples are available at www.bannerengineering.com.

# DXM100-B2 Wireless Controller System Overview

Banner's DXM Logic Controller integrates Banner's wireless radio, cellular connectivity, and local I/O to provide a platform for the Industrial Internet of Things (IIoT).

# I/O Universal Inputs

Discrete Outputs
Courtesy Power
Switch Power
DC Latching Outputs
Analog Outputs
SDI-12 Sensor Interface

# Connectivity

Cellular Sure Cross Radios Ethernet USB RS-485 Master RS-485 Slave

# **Logic Controller**

Action Rules
Programming Language
Scheduler
Push to the Cloud
Data Logging
SMS and Email
SMS Control

# **User Interface**

LCD Screen LED Indicators

Inputs/Outputs - On-board universal and programmable I/O ports connect to local sensors, indicators, and control equipment.

- Universal Inputs
- Discrete outputs
- Courtesy power
- Switch power

- Battery backup
- Solar controller
- DC latching outputs
- SDI-12 sensor interface

Connectivity—The DXM100's wired and wireless connectivity options make it easy to share data between local and remote equipment. The cellular modem option eliminates the need for IT infrastructures to connect remote equipment for sensing and control. The integrated Sure Cross<sup>®</sup> wireless radio enables Modbus connectivity to remote sensors, indicators, and control equipment.

## Wired Connectivity

Ethernet: Modbus TCP or Ethernet/IP

Field Bus: Modbus RS-485 Master/Slave or CAN

#### Wireless Connectivity

Sure Cross Wireless Radio: DX80 900 MHz, DX80 2.4 GHz, MultiHop 900 MHz, or MultiHop 2.4 GHz Cellular modem: CDMA (Verizon) or GSM

Logic Controller—Program the DXM100's logic controller using action rules and/or ScriptBasic language, which can execute concurrently. The control functions allow freedom when creating custom sensing and control sequences. The logic controller supports the Modbus protocol standards for data management, ensuring seamless integration with existing automation systems.

## **Action Rules**

Supports simple logic, arithmetic and thresholding

Low complexity solutions

SMS text message Notifications

E-mail Notifications
Push data on conditions

# **Text Programming Language**

ScriptBasic

Medium complexity solutions

# Scheduler

Time/calendar-based events Astronomical clock

## **Data Logging**

Cyclic Data/Event logging E-mail log files

## **SMS Commanding**

Read/Write Local Registers Force a push to the cloud Reboot controller

**User Interface**—A simple user interface consists of an LCD screen and four LED indicators. Use the LCD to access system status and setup, view user selectable events or data, and to bind and perform site surveys for Sure Cross radios. Configure the user programmable LEDs to indicate the status of the DXM100, processes, or equipment.

## User programmable LCD

Bind Sure Cross Radios Site Survey View Sensor Information System Status

# **User Defined LED indicators**

# Applications Overview

The DXM100-B2 Wireless Controller is ideal for smart factory and facilities applications, including:

- Productivity solutions, such as
  - Call for parts, service, or maintenance
  - Pick-to-light
  - Tank level monitoring
- Predictive maintenance and continuous monitoring using
  - Vibration and temperature monitoring
  - Non-contact temperature monitoring
- Environmental monitoring and control, such as
  - Temperature and humidity monitoring
  - Irrigation and agricultural monitoring

The DXM100-B2 Wireless Controller can provide visual indication using indicator lights, send text or email alerts, collect data, and interface with automation systems.

# Specifications

# MultiHop Radio Specifications

#### Radio Range<sup>1</sup>

900 MHz, 1 Watt: Up to 9.6 km (6 miles) 2.4 GHz, 65 mW: Up to 3.2 km (2 miles)

#### Antenna Minimum Separation Distance

900 MHz, 150 mW and 250 mW: 2 m (6 ft) 900 MHz, 1 Watt: 4.57 m (15 ft) 2.4 GHz, 65 mW: 0.3 m (1 ft)

#### Radio Transmit Power

900 MHz, 1 Watt: 30 dBm (1 W) conducted (up to 36 dBm EIRP) 2.4 GHz, 65 mW: 18 dBm (65 mW) conducted, less than or equal to 20 dBm (100 mW) EIRP

## Spread Spectrum Technology

FHSS (Frequency Hopping Spread Spectrum)

## 900 MHz Compliance (1 Watt)

FCC ID UE3RM1809: FCC Part 15, Subpart C, 15.247 IC: 7044A-RM1809

#### 2.4 GHz Compliance (MultiHop)

FCC ID UE300DX80-2400: FCC Part 15, Subpart C, 15.247 RED Directive 2014/53/EU IC: 7044A-DX8024

# Antenna Connection

Ext. Reverse Polarity SMA, 50 Ohms Max Tightening Torque: 0.45 N·m (4 lbf·in)

## Radio Packet Size (MultiHop)

900 MHz: 175 bytes (85 Modbus registers) 2.4 GHz: 75 bytes (37 Modbus registers)

# RS-485 Communication Specifications

#### Communication Hardware (MultiHop RS-485)

Interface: 2-wire half-duplex RS-485
Baud rates: 9.6k, 19.2k (default), or 38.4k via DIP switches; 1200 and 2400 via the MultiHop Configuration Tool
Data format: 8 data bits, no parity, 1 stop bit

# RS-232 Communication Specifications

#### Communication Hardware (MultiHop RS-232)

Interface: 2-wire RS-232

Baud rates: 9.6k, 19.2k (default), or 38.4k via DIP switches; 1200 and 2400 via the MultiHop Configuration Tool Data format: 8 data bits, no parity, 1 stop bit

# Power and I/O Specifications

#### Supply Voltage

12 to 30 V dc (use only with a suitable Class 2 power supply (UL) or a SELV (CE) power supply) or

12 V dc solar panel and 12 V sealed lead acid battery

# Courtesy Power Out

One output at 5 Volts, 500 mA maximum No short circuit protection

#### Switched Power Outputs

Two adjustable 5 V to 24 V outputs
One SDI-12 adjustable 5 V to 24 V output
5 V: 400 mA maximum
16 V: 125 mA maximum
24 V: 85 mA maximum

# Power Consumption

35 mA average at 12 Volts

## Counters, Synchronous

32-bits unsigned 10 ms clock rate minimum

#### Universal Inputs

Sinking/Sourcing discrete, 4–20 mA analog, 0–10 V analog, counter, and temperature 10 kOhm thermistor

#### Solar Power

12 V sealed lead acid battery 2 A maximum charge current 12 V, 20 W maximum solar panel

# Solar Power Battery Charging

1 A maximum with 20 Watt solar panel

# Communication Protocols

Modbus RTU Master/Slave, Modbus/TCP, and Ethernet/IP

## Security Protocols

VPN, SSL, and HTTPS

# Logging

8 GB maximum; removable Micro SD card format

# Construction

Polycarbonate; DIN rail mount option

## Analog Outputs (DAC)

0 to 10 V dc output Accuracy: 0.1% of full scale +0.01% per °C Resolution: 12-bit

#### Discrete Output Rating (NMOS)

Less than 1 A max current at 30 V dc ON-State Saturation: Less than 0.7 V at 20 mA ON Condition: Less than 0.7 V OFF Condition: Open

Radio range is with the 2 dB antenna that ships with the product. High-gain antennas are available, but the range depends on the environment and line of sight. Always verify your wireless network's range by performing a Site Survey.

# **Environmental Specifications**

#### Operating Conditions<sup>2</sup>

–40 °C to +85 °C (–40 °F to +185 °F) (Electronics); –20 °C to +80 °C (–4 °F to +176 °F) (LCD)

Micro CD Card (if applicable): -25 °C to +85 °C (-13 °F to +185 °F) 95% maximum relative humidity (non-condensing) Radiated Immunity: 10 V/m (EN 61000-4-3)

#### Shock and Vibration

IEC 68-2-6 and IEC 68-2-27 Shock: 30g, 11 millisecond half sine wave, 18 shocks Vibration: 0.5 mm p-p, 10 to 60 Hz

#### **Environmental Rating**

IEC IP20

#### Certifications





(CE approval only applies to 2.4 GHz models)

# Accessories

For a complete list of all the accessories for the Sure Cross wireless product line, please download the *Accessories List* (p/n b\_3147091)

#### Cordsets

MQDC1-506—5-pin M12/Euro-style, straight, single ended, 6 ft MQDC1-530—5-pin M12/Euro-style, straight, single ended, 30 ft MQDC1-506RA—5-pin M12/Euro-style, right-angle, single ended, 6 ft MQDC1-530RA—5-pin M12/Euro-style, right-angle, single ended, 30 ft

#### Static and Surge Suppressor

BWC-LFNBMN-DC—Surge Suppressor, bulkhead, N-Type, dc Blocking, N-Type Female. N-Type Male

#### Short-Range Omni Antennas

BWA-2O2-D—Antenna, Dome, 2.4 GHz, 2 dBi, RP-SMA Box Mount BWA-9O2-D—Antenna, Dome, 900 MHz, 2 dBi, RP-SMA Box Mount BWA-9O2-RA—Antenna, Rubber Fixed Right Angle, 900 MHz, 2 dBi, RP-SMA Male Connector

## Medium-Range Omni Antennas

BWA-9O5-C—Antenna, Rubber Swivel, 900 MHz 5 dBi, RP-SMA Male Connector

BWA-2O5-C—Antenna, Rubber Swivel, 2.4 GHz 5 dBi, RP-SMA Male Connector

## Enclosures and DIN Rail Kits

<code>BWA-AH864</code>—Enclosure, Polycarbonate, with Opaque Cover, 8 × 6 × 4 <code>BWA-AH1084</code>—Enclosure, Polycarbonate, with Opaque Cover, 10 × 8 × 4 <code>BWA-AH12106</code>—Enclosure, Polycarbonate, with Opaque Cover, 12 × 10 × 6

BWA-AH8DR—DIN Rail Kit, 8", 2 trilobular/self-threading screws BWA-AH10DR—DIN Rail Kit, 10", 2 trilobular/self-threading screws BWA-AH12DR—DIN Rail Kit, 12", 2 trilobular/self-threading screws

#### Misc Accessories

BWA-CG.5-3X5.6-10 — Cable Gland Pack: 1/2-inch NPT, Cordgrip for 3 holes of 2.8 to 5.6 mm diam, qty 10

BWA-HW-052 — Cable Gland and Vent Plug Pack: includes 1/2-inch NPT gland, 1/2-inch NPT multi-cable gland, and 1/2-inch NPT vent plug, qty 1 each

#### Antenna Cables

BWC-1MRSMN05—LMR100 RP-SMA to N-Type Male, 0.5 m BWC-2MRSFRS6—LMR200, RP-SMA Male to RP-SMA Female Bulkhead, 6 m

BWC-4MNFN6-LMR400 N-Type Male to N-Type Female, 6 m

#### Long-Range Omni Antennas

BWA-908-AS—Antenna, Fiberglass, 3/4 Wave, 900 MHz, 8 dBi, N-Type Female Connector

BWA-2O8-A—Antenna, Fiberglass, 2.4 GHz, 8 dBi, N-Type Female Connector

## Long-Range Yagi Antennas

BWA-9Y10-A—Antenna, 900 MHz, 10 dBd, N-Type Female Connector

# **Power Supplies**

 $\mbox{\it PSD-24-4}-\mbox{\it DC}$  Power Supply, Desktop style, 3.9 A, 24 V dc, Class 2, 4-pin M12/Euro-style quick disconnect (QD)

*PSDINP-24-13* — DC Power Supply, 1.3 Amps, 24 V dc, with DIN Rail Mount, Class I Division 2 (Groups A, B, C, D) Rated

PSDINP-24-25 — DC Power Supply, 2.5 Amps, 24 V dc, with DIN Rail Mount, Class I Division 2 (Groups A, B, C, D) Rated

BWA-SOLAR PANEL 20W—Solar Panel, 12 V, 20 W, Multicrystalline,  $573 \times 357 \times 30$ , "L" style mounting bracket included (does not include controller)

# Warnings

Install and properly ground a qualified surge suppressor when installing a remote antenna system. Remote antenna configurations installed without surge suppressors invalidate the manufacturer's warranty. Keep the ground wire as short as possible and make all ground connections to a single-point ground system to ensure no ground loops are created. No surge suppressor can absorb all lightning strikes; do not touch the Sure Cross® device or any equipment connected to the Sure Cross device during a thunderstorm.

Exporting Sure Cross® Radios. It is our intent to fully comply with all national and regional regulations regarding radio frequency emissions. Customers who want to re-export this product to a country other than that to which it was sold must ensure the device is approved in the destination country. A list of approved countries appears in the Radio Certifications section of the product manual. The Sure Cross wireless products were certified for use in these countries using the antenna that ships with the product. When using other antennas, verify you are not exceeding the transmit power levels allowed by local governing agencies. Consult with Banner Engineering Corp. if the destination country is not on this list.

<sup>2</sup> Operating the devices at the maximum operating conditions for extended periods can shorten the life of the device.

# Banner Engineering Corp. Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change; Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to: <a href="https://www.bannerengineering.com">www.bannerengineering.com</a>.

For patent information, see www.bannerengineering.com/patents.

