



SPECIFICATION


- · Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- · Samsung P/N: · Description :
- CL21A476MQCLRNC CAP, 47uF, 6.3V, ±20%, X5R, 0805

(Reference sheet)

A. Samsung Part Number

			<u>CL</u> ①	<mark>21</mark> ②	<u>▲</u> ③	<u>476</u> ④	<u>M</u> 5	<mark>Q</mark> 6	<u>C</u> ⑦	<u>L</u> 8	<u>R</u> 9	<u>N</u> 10	<u>С</u> Ш		
1	Series	Samsung Multi-layer Ceramic Capacitor													
2	Size	0805	(inch c	ode)	de) L: 2.00 ± 0.20 mm W: 1.25 ± 0.20 mm										
							8	Thick	ness	divis	sion		Low profile		
3	Dielectric	X5R			Inner electrode				Ni						
4	Capacitance	47	uF					Term	inatio	on			Cu		
5	Capacitance	±20	%					Platir	ng				Sn 100%	(Pb Free)	
	tolerance						9	Prod	uct				Size control	code	
6	Rated Voltage	6.3	V				10	Spec	ial				Reserved for	r future use	
\bigcirc	Thickness	0.85 ± 0.	5 ± 0.10 mm (1		1	Packaging				Cardboard Type, 7" reel					

B. Structure & Dimension



Samsung P/N	Dimension(mm)								
Samsung F/N	L	W	Т	BW					
CL21A476MQCLRNC	2.00 ± 0.20	1.25 ± 0.20	0.85 ± 0.10	0.50 +0.20/-0.30					

C. Samsung Reliablility Test and Judgement Condition

	Judgement	Test condition					
Capacitance	Within specified tolerance	120Hz ±20% / 0.5±0.1Vrms					
Tan δ (DF)	0.1 max.	*A capacitor prior to measuring the capacitance is heat treated at $150^{\circ}C$ +0/-10°C for 1 hour and maintained in ambient air for 24±2 hours.					
Insulation	10,000Mohm or 100Mohm× <i>μ</i> F	Rated Voltage 60~120 sec.					
Resistance	Whichever is smaller						
Appearance	No abnormal exterior appearance	Microscope (×10)					
Withstanding	No dielectric breakdown or	250% of the rated voltage					
Voltage	mechanical breakdown						
Temperature	X5R						
Characteristics	(From-55 ℃ to 85 ℃, Capacitance change sh	ould be within ±15%)					
Adhesive Strength	No peeling shall be occur on the	500g·f, for 10±1 sec.					
of Termination	terminal electrode						
Bending Strength	Capacitance change : within ±12.5%	Bending to the limit (1mm)					
		with 1.0mm/sec.					
Solderability	More than 75% of terminal surface	SnAg3.0Cu0.5 solder					
	is to be soldered newly	245±5℃, 3±0.3sec.					
		(preheating : 80~120℃ for 10~30sec.)					
Resistance to	Capacitance change : within ±7.5%	Solder pot : 270±5℃, 10±1sec.					
Soldering Heat	Tan δ, IR : initial spec.						
Vibration Test	Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.)					
		2hours × 3 direction (x, y, z)					
Moisture	Capacitance change : within ±12.5%	With rated voltage					
Resistance	Tan δ: 0.2 max	40±2℃, 90~95%RH, 500+12/-0hrs					
	IR : 500Mohm or 12.5Mohm × μ F						
	Whichever is smaller	100% cu i i u					
High Temperature	Capacitance change : within ±12.5%	With 100% of the rated voltage					
Resistance	Tan δ: 0.2 max	Max. operating temperature					
	IR : 1,000Mohm or 25Mohm × μ F	1000+48/-0hrs					
	Whichever is smaller						
Temperature	Capacitance change : within ±7.5%	1 cycle condition					
Cycling	Tan δ, IR : initial spec.	Min. operating temperature $\rightarrow 25^{\circ}C$					
		\rightarrow Max. operating temperature \rightarrow 25°C					
		E suela fast					
		5 cycle test					

st The reliability test condition can be replaced by the corresponding accelerated test condition.

D. Recommended Soldering method :


Reflow (Reflow Peak Temperature : 260+0/-5°C, 10sec. Max)

Product specifications included in the specifications are effective as of March 1, 2013. Please be advised that they are standard product specifications for reference only. We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications,

please contact our sales personnel or application engineers.



This product ,which guarantees High Temperature Reliability Test with 100% of rated voltage at the maximum temperature, recommended to be used in the circuit with derat is recommended to be used in the circuit with derated voltage compared to the rated voltage of the capacitor for long lifetime.


Max. voltage(V_{Max}) and DC voltage(V_{DC}) applied to this product shown in the table below are recommended to be used under the following conditions for long lifetime, respectively.

[Recommendations for long lifetime]

- $\cdot V_{Max} \leq$ (Derated Voltage on the left graph)
- $\cdot V_{DC} \leq 70\% \times (Derated Voltage on the left graph)$

* Temperature of MLCC : Surface temperature of MLCC in the circuit.

[Types of voltage applied to the capacitor]



Disclaimer & Limitation of Use and Application

The products listed in this Specification sheet are **NOT** designed and manufactured for any use and applications set forth below.

Please note that any misuse of the products deviating from products specifications or information provided in this Spec sheet may cause serious property damages or personal injury. We will **NOT** be liable for any damages resulting from any misuse of the products, specifically including using the products for high reliability applications as listed below.

If you have any questions regarding this 'Limitation of Use and Application', you should first contact our sales personnel or application engineers.

- Aerospace/Aviation equipment
- 2 Automotive or Transportation equipment (vehicles, trains, ships, etc)
- 3 Medical equipment
- ④ Military equipment
- *⑤* Disaster prevention/crime prevention equipment
- 6 Power plant control equipment
- ⑦ Atomic energy-related equipment
- ⑧ Undersea equipment
- Iraffic signal equipment
- Data-processing equipment
- ① Electric heating apparatus, burning equipment
- 2 Safety equipment
- 1 Any other applications with the same as or similar complexity or reliability to the applications