



2-IN-1 SPOT & ANIMATION LED MOVING HEAD WITH DMX CONTROL

MHSPOT30-FX

Particularly dynamic moving head featuring a ring of 12 RGB SMD5050 LED and a powerful white 30W LED.

- 14 or 16 DMX channels
- Operating modes: Auto, sound, DMX or Master/slave
- 7-color wheel + white and rainbow effect
- 7-gobo wheel + open and gobo shake
- 540° pan and 190° tilt rotation
- Strobe 1 – 20 flashes per second
- Dimmer
- Manual focus
- LED display
- 13° spot angle

**EAN
CODE**

**5420047136060
16-2003**

SPECIFICATIONS TECHNIQUES

Power supply	100-240Vac 50/60Hz
Consumption	55W
Dimensions	160 x 145 x 300mm
Weight	2.65kg



LOGISTICS VALUES

EAN14 code 54200471360608

