

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0879160111](#)
Status: **Active**
Description: 1.00mm Pitch DDR-2 DIMM Socket, 22.5 Degree Angle, Through Hole, 240 Circuits, 1.8V Voltage Key, 0.76µm Gold (Au) Plating, 4.00mm Tail Length, with Off-White Latches, Lead-Free

Documents:

[3D Model](#) [Product Specification PS-87916-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Memory Module Sockets
 Series [87916](#)
 Component Type Socket
 Electrical Model Yes
 JEDEC Outline MO-237
 Product Name DDR2 DIMM
 UPC 800756936642

Physical


Circuits (Loaded) 240
 Circuits (maximum) 240
 Durability (mating cycles max) 25
 Entry Angle 22.5° Angle
 Flammability 94V-0
 Function Key None
 Housing Color Black
 Keying to Mating Part Yes
 Latch Color Natural (Off-White)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 11.331/g
 PC Tail Length 4.00mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 3.20mm
 Packaging Type Tray
 Pitch - Mating Interface 1.00mm
 Pitch - Termination Interface 1.00mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Temperature Range - Operating -55° to +85°C
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 30V AC (RMS)/DC
 Voltage Key Center

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
 Lead-free Process Capability SMC&WAVE
 Max. Cycles at Max. Process Temperature 002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87916 Series](#)

Mates With

JEDEC Standard 1.27mm Modules

Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-87916-001
Product Specification	PS-87916-001-001
S-Parameter Model	SP-87916-001
Sales Drawing	SD-87916-001

This document was generated on 10/08/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION