

# Toroids (5952020601)



Part Number: 5952020601

52 TOROID

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- 9th digit 1 = Parylene Coating, 2 = Thermo- Set Plastic Coating

**A ring configuration provides the ultimate utilization of the intrinsic ferrite material properties. Toroidal cores are used in a wide variety of applications such as power input filters, ground- fault interrupters, common- mode filters and in pulse and broadband transformers.**

□All toroidal cores are supplied burnished to break sharp edges.

Coating Options:


- Toroids with an outside diameter of 9.5 mm (0.375") or smaller can be supplied Parylene C coated. The Parylene coating will increase the "A" and "C" dimensions and decrease the "B" dimension a maximum of 0.038 mm (0.0015"). The ninth digit of a Parylene coated toroid part number is a "1". See reference tables for the material characteristics of Parylene C. Parylene C coating is RoHS compliant.
- Toroids with an outside diameter of 9.5 mm (0.375") or larger can be supplied with a uniform coating of thermo- set plastic coating. This coating will increase the "A" and "C" dimensions and decrease the "B" dimension a maximum of 0.5 mm (0.020"). The 9th digit of the thermo- set plastic coated toroid part number is a "2". Thermo- set plastic coating is RoHS compliant.
- Thermo- set plastic coated parts can withstand a minimum breakdown voltage of 1000 Vrms, uniformly applied across the "C" dimension of the toroid.

□For any toroidal core requirement not listed in the catalog, please contact our customer service department for availability and pricing.

The □C□ dimension may be modified to suit specific applications.


Weight: 7.54 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	21.7	±0.40	0.854	-
B	13.5	±0.30	0.531	-
C	6.35	±0.25	0.25	-



**Chart Legend**

$\Sigma l / A$  : Core Constant,  $l_c$  : Effective Path Length,  $A_c$  : Effective Cross- Sectional Area,  $V_c$  : Effective Core Volume

$A_L$  : Inductance Factor 

Electrical Properties	
$A_L$ (nH)	151 ±25%
$A_e$ (cm <sup>2</sup> )	0.256
$\Sigma l / A$ (cm <sup>-1</sup> )	20.8
$l_c$ (cm)	5.33
$V_c$ (cm <sup>3</sup> )	1.368

Toroids are tested for  $A_L$  values at 10 kHz.

Fair- Rite Products Corp. • One Commercial Row, Wallkill, New York 12589-0288

888-324-7748 • 845-895-2055 • Fax: 845-895-2629 • [ferrites@fair-rite.com](mailto:ferrites@fair-rite.com) • [www.fair-rite.com](http://www.fair-rite.com)