
Resistors

Metal Foil on Ceramic Chip Resistors

MFC Series

- Small size down to 0603
- TCR down to ±30ppm/°C
- Current sensing for power electronics
- High power density
- 2817 & 4320 AEC-Q200 Qualified






All parts are Pb-free and comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		0603	2817	4320		
Power rating @70°C	W	0.5	5	5		
Overload rating 5s	W	2.5	25	25		
Resistance range	mΩ	5 to 20	3 to 150	2 to 50		
Standard values	mΩ	5, 7, 9, 10, 20	E24 preferred, other values on request	2, 4, 5, 6, 8, 9, 10, 15, 20, 30, 33, 40, 50		
Tolerance	%	± 1, 5	±1			
TCR (+25°C to +125°C)	ppm/°C	± 50	±30			
Operating temperature	°C	-55 to +155				

Physical Data

Dimensions in mm and nominal weight in mg								
	Size	L ±0.30	W ±0.25	H ±0.20	A max	В	Wt. nom	
	0603	1.6	0.8	0.6	0.6	0.4±0.2	3.3	
	2817	7.1	4.2	0.7	1.0	1.3±0.5	80 to 140	Н
	4320	11.0	5.0	0.65	1.0	2.5±0.3	140 to 180	



Construction

Metal foil resistor material is bonded onto a 96% alumina substrate and protected. Wrap-around terminations have an electroplated nickel barrier and solder coating. 0603 size parts have the foil on the upper surface whilst 2817 & 4320 size parts have the foil on the lower surface.


Marking

0603 size parts are not marked. 2817 & 4320 size parts are marked with ohmic value only. Reels are marked with type, value, tolerance, date code and quantity.

Solvent Resistance

The body protection is resistant to all normal industrial cleaning solvents suitable for printed circuits.

Recommended Pad Dimensions



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies IRC Welwyn



MFC Series

Performance Data

Parameter		Maximum (+0.001Ω)				
Parameter	0603	2817	4320			
Load at rated power: 1000 hours at 70°C, cyclic load	±∆R%	1	5			
Overload: 5 x rated power for 5 seconds	±ΔR%	1	5			
Moisture: No load, 1000 hours 85°C, 85% RH	±ΔR%	1				
Temperature rapid change: 100 cycles,-55°C & 155°C	±ΔR%	1		0.5		
High temperature exposure: 1000 hours at 155°C	±ΔR%		1			
Low temperature exposure: 1000 hours at-55°C	±ΔR%	1				
Bend strength: 2mm deflection	±ΔR%	0.5		1		
Resistance to solder heat: 260±5°C for 10s	±ΔR%	0.5				
Solderability: 245±5°C for 2s		≥95% coverage				
Insulation resistance: 100V DC for 1min	ohms	>100M				

175 <u>ဂ</u>

150

125

100

75

50

25 0

0%

20%

Rise (


Temperature

Thermal Data

4320 Typical Temperature Rise

Temperature Rise (°C) 175 Hotspot, R050 150 125 100 75 50 Terminal, R002 Termianl, R050 25 0% 20% 40% 60% 80% 100%

Proportion of Rated Power Temperature Derating



2817 & 4320 Terminal Temperature (°C)


2817 Typical Temperature Rise mounted on high T_g FR4 board)

Hotspot, R100 Hotspot, R003

Proportion of Rated Power

Ordering Procedure

Example: MFC0603-R005FT5 (MFC0603, 5 milliohms ±1%, Pb-free)



1	2	3	4	5		5
Series	Size	Value	Tolerance		Packing	
MFC	0603	3/4 characters	F = ±1%	T5	0603	5000/reel
IVIFC	2817			T1	2817	1000/reel
	4320	R = ohms	J = ±5%	T1	4320	1000/reel

Packaging

0603 size resistors are supplied on 8mm paper carrier tape and 2817 size resistors are supplied on 12mm embossed carrier tape, all on 7 inch reels as per IEC 286-3.

4320 size resistors are supplied on 24mm carrier tape, all on 13 inch reels as per IEC 286-3.

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print. BI Technologies IRC Welwyn

Terminal, R100