


**KEMET Part Number: C052C121J2G5TA**  
(C052C121J2G5TA)

LDD Comm C0G, Ceramic, 120 pF, 5%, 200 VDC, C0G, Lead Spacing = 5.08mm



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	LDD Comm C0G
<b>Style:</b>	Radial
<b>Features:</b>	Commercial
<b>RoHS:</b>	With Exemptions
<b>REACH:</b>	SVHC (Pb – CAS 7439-92-1)
<b>Termination:</b>	Tin
<b>Failure Rate:</b>	N/A

**Dimensions**

<b>L</b>	4.83mm +/-0.25mm
<b>H</b>	4.83mm +/-0.25mm
<b>T</b>	2.29mm +/-0.25mm
<b>S</b>	5.08mm +/-0.38mm
<b>LL</b>	31.75mm MIN
<b>F</b>	0.635mm +0.102/-0.051mm
<b>G</b>	1.143mm MAX

**Specifications**

<b>Capacitance:</b>	120 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	200 VDC
<b>Dielectric Withstanding Voltage:</b>	500 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	C0G
<b>Dissipation Factor:</b>	0.10% 1MHz 25C
<b>Insulation Resistance:</b>	8.333 GOhms

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	100

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.