

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0462070004](#)

Status: **Active**

Overview: [Mini-Fit Jr. Power Connectors](#)

Description: 4.20mm Pitch, Mini-Fit Jr. Reflow Solder Capable, Tray Header, Dual Row, Vertical, 4 Circuits, 1.57mm PCB Thickness, with PCB Pegs, LCP Housing, with Tin (Sn) Over Nickel (Ni) Plating, Glow-Wire Capable, Tray

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-5556-001-001 \(PDF\)](#)

[Packaging Specification PK-46207-001-000 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [46207](#)
Application Board-to-Board, Power, Wire-to-Board
Comments Current for wire-to-wire applications = 13.0A max. per circuit. Current for wire-to-board applications = 9.0A max. per circuit
Overview [Mini-Fit Jr. Power Connectors](#)
Product Name Mini-Fit Jr.
UPC 800756675756

Physical

Breakaway No
Circuits (Loaded) 4
Circuits (maximum) 4
Color - Resin Black
Durability (mating cycles max) 100
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable Yes
Guide to Mating Part No
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Matte Tin
Material - Plating Termination Matte Tin
Material - Resin High Temperature Thermoplastic
Net Weight 1.715/g
Number of Rows 2
Orientation Vertical
PC Tail Length 3.66mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Pitch - Mating Interface 4.20mm
Pitch - Termination Interface 4.20mm
Polarized to Mating Part Yes
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46207](#) Series

Mates With

[45750](#) Terminal, [5557](#) Mini Fit Jr. Receptacle

Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46207-001-000
Product Specification	PS-5556-001-001
Sales Drawing	SD-46207-001-000

This document was generated on 10/19/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION