




REVISION RECORD			
REV.	CONTENT	MOD.	DATE
△	New Publish		



Insulated  
Double-side  
Adhesive




①

Section B-B

View C

Notes:

1. Pitch: 2.54mm
- 2.1 Terminal Strip: 630 Tie-point
- 3.2 Distribution Strips: 200 Tie-point
4. Rated voltage/current: 3 0 0 V / 3-5 A
5. Insulation resistance: 500MΩ/DC500V
6. Withstanding voltage: AC1000V/1Min
7. Wire range: 29~20 AWG
8. Temp. Range: -25° c ~ +80° c
- Strip length: 7-8mm
9. Undimensioned Tolerances:



TOLERANCES EXCEPT AS NOTED

variable range	linear dimension				fillet	chamfer	short angle sid				≡	—	□	//	⊥	
	to 6	over 6 to 30	over 30 to 120	over 120 to 480	all	over 6 to 6	over 10 to 10	over 50 to 50	over 120 to 120	all	to 5	over 5 to 30	over 30 to 120	over 120 to 120		
tolerance	±0.1	±0.2	±0.3	±0.5	±0.2	±0.5	±1	1°	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

2	BB-102-2-72	700217201A	1	Terminal Strip
1	BB-102-1-72	700117201A	2	Distribution Strips
NO.	NAME OF PART	NO. OF PART	Q' TY	NOTES
DES.	WJY	DATE 08/22/11"	UNITS mm	FIRST ANGLE PROJECTION
CHK.	DATE	SIZE A4		1 of 1
APP.	DATE	SCALE 1:1	DWG NO.	SP-2-7005001
TITLE				BB-102T
				BB-102T(72 Transparent)