

# UL1015 Style Stranded Hook-Up Wire

pro-POWER




RoHS  
Compliant

This stranded Hook-Up Wire meets the specifications of UL AWM/Style 1015 - 105°C / 600V. UL recognized (UL file no. E352035).

## Specifications

Conductor Material : Stranded Tinned Copper  
Insulation Material : PVC  
Rated Temperature : 105°C  
Rated Voltage : 600V  
Cable Length : Available in 305m Reel or in per metre length

## Diagram



## Marking

E352035 AWM \*\*\*\* \*\*AWG \*\*\*C \*\*\*V VW-1 NEWARK CORP C AWM \*\*AWG I A \*\*\*C \*\*\*V FT-1

Wire Style Number      AWG-No      Rated Temperature      Rated Voltage      AWG-No      Rated Temperature      Rated Voltage

AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/km)	Insulation Colour	Part Number
14	41/0.254	1.88	3.5	8.62	Black	PP002347
					Blue	PP002348
					Brown	PP002349
					Green/Yellow	PP002350
					Red	PP002351
					Yellow	PP002352
16	65/0.16	1.49	3.1	13.7	Green/Yellow	PP002353
18	34/0.18	1.21	2.8	21.86	Orange	PP002354
					Grey	PP002355
20	21/0.18	0.95	2.5	34.6	Orange	PP002356
20	21/0.18	0.95	2.5	34.6	Grey	PP002357
					Purple	PP002358
					White	PP002359
					Yellow	PP002360

# UL1015 Style Stranded Hook-Up Wire

pro-POWER

AWG	Construction # Strands/Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Insulation Colour	Part Number
22	17/0.16	0.76	2.3	55	Green/Yellow	PP002361
22	17/0.16	0.76	2.3	55	Yellow	PP002362
24	11/0.16	0.61	2.2	93.25	Black	PP002363
					Red	PP002364
					White	PP002365

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)  
[www.cpc.co.uk](http://www.cpc.co.uk)

pro-POWER