

Product data sheet

Connectors for medical applications




Product description **Contacts: 8, female panel mount connector, lightgrey, solder**

Area **Snap-in IP67, subminiature Series 620 MED**
Order number **99 9228 400 08**


Illustration



Scale drawing



Contact arrangement



	X	Y
1	0,96	-1,98
2	2,15	-0,49
3	1,72	1,37
4	0,00	2,20
5	-1,72	1,37
6	-2,15	-0,49
7	-0,96	-1,98
8	0,00	0,00

You can find the assembly instructions on the next page.

Technical data

General values

Connector design	female panel mount connector
Connector locking system	snap
Termination	solder
Wire gauge (mm)	0,25 mm ²
Wire gauge (AWG)	24
Upper limit temperature	85 °C
Lower limit temperature	-25 °C

Electrical values

Rated current (40 °C)	1 A
Rated voltage	63 V
Rated impulse voltage	800 V
Pollution degree	2
Overvoltage category	II
Insulating material group	II
Volume resistivity	≤ 3 mΩ
Insulation resistance	≥ 10 ¹⁰ Ω
EMC compliance	Shielding is not possible
Degree of protection	IP67

Material

Contact material	CuZn (brass)
Contact plating	Au (gold)
Contact body material	PA (UL 94 V-0)
Housing material	PA

Product description

Contacts: 8, female panel mount connector, lightgrey, solder


Area

Snap-in IP67, subminiature Series 620 MED

Order number

99 9228 400 08

Assembly instructions / Panel cut-out



Product description	Contacts: 8, female panel mount connector, lightgrey, solder
Area	Snap-in IP67, subminiature Series 620 MED
Order number	99 9228 400 08

Security notices

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.

Connectors with degree of protection IP 67 and IP 68 are not suitable for use under water. When used outdoors, the connectors must be separately protected against corrosion. For further information about IP degrees of protection refer to 'Technical support' in the Download Centre.