


P2550

Non-Replaceable Probe - Epoxy Mount

Product Family: Pylon



Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 1.00 (28.00) - 3.20 (91.00) - Stainless Steel, Gold plated

High - 4.00 (113.00) - 6.70 (190.00) - Stainless Steel, Gold plated

Mechanical:

Test Center (mil): 187

Test Center (mm): 4.75

Overall Length (mil): 1,453

Overall Length (mm): 36.91

Full Travel (mil): 250

Full Travel (mm): 6.35

Recommended Travel (mil): 167

Recommended Travel (mm): 4.24

Rec. Mounting Hole Size (mil): 126

Rec. Mounting Hole Size (mm): 3.20

Recommended Drill Size: #30 or 3.20 mm

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 5

Average DC Resistance lower than (mOhm): 30

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over hard Nickel

Barrel Material: Brass, Gold plated


Ball Material: Stainless Steel, Gold plated

TIPS:


Tip Materials: BeCu

Tips:


P2550-0-8



P2550-6-8



P2550-8



P2550-9

