

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151370500](#)
Status: **Active**
Overview: [Mini-Lock Wire-to-Board Connector System](#)
Description: Mini-Lock-to-Mini-Lock Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Female-Female, Single Row, 50.00mm Length, 5 Circuits, Natural

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 15137 |
| Application | Signal, Wire-to-Board |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Mini-Lock-to-Mini-Lock |
| Overmolded | No |
| Overview | Mini-Lock Wire-to-Board Connector System |
| Product Name | Mini-Lock |
| UPC | 191128925426 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 50.00mm |
| Circuits (Loaded) | 5 |
| Color - Resin | Natural |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Polyester |
| Net Weight | 3.880/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.50mm |
| Plating min - Mating | 0.889µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Size AWG | 22 |
| Wire/Cable Type | UL 1061 |


Electrical

| | |
|-------------------|------------------|
| Voltage - Maximum | 250V AC (RMS)/DC |
|-------------------|------------------|

Material Info

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 151370500-000 |
|---------------|---------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15137 Series](#)

Mates With

[53375](#) , [53426](#)