### Model HA72L-0630 series



#### **Features:**

- Operating Temperature Range –55°C to +155°C
- Ambient Temperature, Maximum +115°C
- Temperature Rise, 40°C
- RoHS Compliant
- AEC-Q200 Certified



All parts are Pb-free and comply with EU Directive 2011/65/EU (RoHS2)

## Schematic



Specifications @ 25°C

Part Number	Inductance (µH ±20% @0A	DCR (mΩ) Typ	DCR (mΩ) Max	Irms (A)	Isat (A)	Part Number	Inductance (µH ±20% @0A	DCR (mΩ) Typ.	DCR (mΩ) Max	Irms (A)	Isat (A)
HA72L-0630R10LFTR	0.10	1.5	1.7	32.5	60.0	HA72L-06301R5LFTR	1.50	14.0	15.0	9.0	18.0
HA72L-0630R15LFTR	0.15	1.9	2.5	26.0	52.0	HA72L-06302R2LFTR	2.20	18.0	20.0	8.0	14.0
HA72L-0630R20LFTR	0.20	2.4	3.0	24.0	41.0	HA72L-06303R3LFTR	3.30	28.0	30.0	6.0	13.5
HA72L-0630R22LFTR	0.22	2.5	2.8	23.0	40.0	HA72L-06304R7LFTR	4.70	37.0	40.0	5.5	10.0
HA72L-0630R33LFTR	0.33	3.5	3.9	20.0	30.0	HA72L-06305R6LFTR	5.60	52.0	60.0	4.8	10.0
HA72L-0630R47LFTR	0.47	4.0	4.2	17.5	26.0	HA72L-06306R8LFTR	6.80	54.0	60.0	4.5	8.0
HA72L-0630R56LFTR	0.56	5.0	5.5	15.5	25.0	HA72L-06308R2LFTR	8.20	64.0	68.0	4.0	7.5
HA72L-0630R68LFTR	0.68	5.0	5.5	15.5	25.0	HA72L-0630100LFTR	10.0	102.0	105.0	3.0	7.0
HA72L-0630R82LFTR	0.82	6.7	8.0	13.0	24.0	HA72L-0630150LFTR	15.0	110.0	125.0	3.5	3.0
HA72L-06301R0LFTR	1.00	9.0	10.0	11.0	22.0	HA72L-0630220LFTR	22.0	129.0	135.0	2.9	2.5


Notes: (1) Isat is the saturation current at which inductance rolls off approximately 30% from its initial (zero DC)


- (2) Irms is the approximate current at which  $\Delta T = 40^{\circ}C$
- (3) Operating Temperature Range –55°C to +155°C


### Model HA72L-0630 series





### Electrical Characteristics @ 25°C





















### Model HA72L-0630 series





#### Electrical Characteristics @ 25°C




















General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


TT Electronics | BI Technologies
A-1445, Jalan Tanjung Api
25050 Kuantan Pahang Darul Makmur, Malaysia | Ph: +60 9 565 8888
www.ttelectronicsmagnetics.com/customer-service-enquiry


### Model HA72L-0630 series





#### Electrical Characteristics @ 25°C












### Model HA72L-0630 series



## **Outline Dimensions (mm)**



CASE SIZE	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	G(mm)	H(mm)	
0630 series	6.6 ± 0.3	7.1 ± 0.3	3	3.0 ± 0.3	1.6 ± 0.5	7.40	3.70	3.50	

### **Packaging**

	Embossed Tape and Reel						
Standard:	Reel:	Diameter	All case size	=	13" (330mm)		
		Capacity	Case size 0630	=	1,000 units		

## **Ordering information**

