

## **Power PCB Relay RT1 Inrush**

- 1 pole 16A, 1 form C (CO) or 1 form A (NO) contact
- For inrush peak currents up to 80A
- Mono- or bistable coil
- 5kV/10mm coil-contact
- **■** Reinforced insulation
- Ambient temperature 85°C
- WG version: product in accordance to IEC 60335-1

Typical applications
Domestic appliances, heating control, lighting control



F0177-C



| Approvals  |  |
|--|--|
| VDE Cert. No. 40007571, UL E214025, cCSAus 1142018 |  |
| Technical data of approved types on request        |  |

| Contact Data                              |                                |
|---|--------------------------------|
| Contact arrangement                       | 1 form C (CO) or 1 form A (NO) |
| Rated voltage                             | 250VAC                         |
| Max. switching voltage                    | 400VAC                         |
| Rated current                             | 16A                            |
| Limiting continuous current               | 16A, UL: 20A (K-version)       |
| Limiting making current,                  |                                |
| max. 4s, df 10%                           | 30A                            |
| max. 20ms (incandescent lamps), RT3       | 33L version 80A                |
| Breaking capacity max.                    | 4000VA                         |
| Contact material                          | AgNi90/10, AgSnO               |
| Frequency of operation, with/without loa  | ad 360/72000h <sup>-1</sup>    |
| Operate/release time max., DC coil        | 9/6ms                          |
| Operate/Reset time max., bistable version | on 10/10ms                     |
| Bounce time max., form A/form B           | 3/6ms                          |

| Contact | t ratings |
|---------|-----------|
|         |           |

| Туре             | Contact    | Load                                | Cycles             |
|------------------|------------|-------------------------------------|--------------------|
| <b>IEC 61810</b> | )          |                                     |                    |
| RT33L            | A (NO)     | 16A, 250VAC resistive, 85°C         | $50x10^3$          |
| RT33L            | A (NO)     | 10A, 400VAC resistive, 85°C         | 10x10 <sup>3</sup> |
| RT31             | C (CO)     | 16A, 250VAC resistive, 85°C         | 6x10 <sup>3</sup>  |
| RT33K            | A (NO)     | 16A, 250VAC resistive, 85°C         | $30x10^3$          |
| UL 508           |            |                                     |                    |
| RT33K            | A (NO)     | 20A, 277VAC general purpose, 40°C   | 10x10 <sup>3</sup> |
| RT33L            | A (NO)     | 16A, 250VAC resistive, 85°C         | $50x10^3$          |
| RT31             | C (CO)     | 16A, 250VAC resistive, 85°C         | 6x10 <sup>3</sup>  |
| RT33L            | A (NO)     | 1000W Tungsten, 120VAC, 60 Hz, 40°C | $6x10^{3}$         |
| RT33L            | A (NO)     | 1000W standard ballast,             |                    |
|                  |            | 120VAC, 60 Hz, 40°C                 | 6x10 <sup>3</sup>  |
| EN 60947         | -4-1       |                                     |                    |
| RT31L/RT         | 33L A (NO) | 250V/6A, AC-3                       | 6.050              |
|                  |            |                                     |                    |

RT31L/RT33L A (NO) 250V/6A, AC-3 Mechanical endurance

300 200

monostable version bistable version

| 1a | ax. E | OC loa | ad bre | akin | g ca         | pacity                      | _                |
|----|-------|--------|--------|------|--------------|-----------------------------|------------------|
|    |       | ΝШ     |        |      |              |                             | Cycles<br>Cycles |
|    |       | Ш      |        | res  | sistive      | load                        | 0                |
| _  | +     | Ж      |        | Н    | Ш            |                             | 10               |
|    | Ŧ     |        |        |      |              |                             | 1                |
|    |       | ш      |        | Ų.   | Ш            |                             |                  |
| _  |       |        |        | H    | <del>}</del> |                             | 10               |
| -  | +     | +++    |        | +    | Ш            |                             | -                |
|    |       |        |        |      |              |                             | 10               |
| 1  | 0,2   | 0,5    | 1      | 2    | 5<br>DC      | 10 20<br>current [ <i>A</i> | \] S033:         |
|    |       |        |        |      |              |                             |                  |

| Elec                | trica   | l en | dura | nce |                 |                    |                |
|---------------------|---------|------|------|-----|-----------------|--------------------|----------------|
| \$ 10 <sup>7</sup>  |         |      |      |     |                 |                    |                |
| $\vdash$            |         |      |      |     | 250V/<br>resist | AC<br>ive loa<br>I | d —            |
| 10 <sup>6</sup> AgN | li90/10 |      |      | 16  | ΑΞ              |                    |                |
|                     |         |      |      |     |                 |                    | $\equiv$       |
| 105                 |         |      |      |     |                 |                    |                |
| 10 <sup>4</sup>     |         |      |      |     |                 |                    |                |
| 0 2<br>S0332-B      | 2 4     | 1    | 6 1  |     |                 |                    | 4 16<br>nt [A] |

>30x106 operations

>5x106 operations


| Coil Data, DC coil                  |             |  |
|-------------------------------------|-------------|--|
| Coil voltage range                  | 5 to 110VDC |  |
| Operative range, IEC 61810          | 2           |  |
| Coil insulation system according UL | class F     |  |

|      |           | _  |     |
|------|-----------|----|-----|
| Coil | versions. | DC | COL |

| Coil | Rated   | Operate | Release | Coil                   | Rated coil |
|------|---------|---------|---------|------------------------|------------|
| code | voltage | voltage | voltage | resistance             | power      |
|      | VDC     | VDC     | VDC     | $\Omega \pm 10\%^{1)}$ | mW         |
| 005  | 5       | 3.5     | 0.5     | 62                     | 403        |
| 006  | 6       | 4.2     | 0.6     | 90                     | 400        |
| 012  | 12      | 8.4     | 1.2     | 360                    | 400        |
| 024  | 24      | 16.8    | 2.4     | 1440                   | 400        |
| 048  | 48      | 33.6    | 4.8     | 5520                   | 417        |
| 060  | 60      | 42.0    | 6.0     | 8570 <sup>1)</sup>     | 420        |
|      |         |         |         |                        |            |

1) Coil resistance ±12%.

All figures are given for coil without pre-energization, at ambient temperature  $\pm 23^{\circ}$ C. Other coil voltages on request.



| Coil Data, bistable coils               | 1 coil      | 2 coils             |
|---|-------------|---------------------|
| Magnetic system                         | polariz     | zed, bistable       |
| Coil voltage range                      | 5 t         | o 24VDC             |
| Operative range, IEC 61810              |             | 2                   |
| Limiting voltage, % of rated coil volta | ge 120%     | 150%                |
| Min./Max. energization duration         | 30ms/1min a | it <10% duty factor |
| Coil insulation system according UL     | (           | class F             |



## Power PCB Relay RT1 Inrush (Continued)

## Coil Data (continued)


| Coll | versions, | bistab | e coil |
|------|-----------|--------|--------|
| Coil | Ra        | ated   | Se     |


| Coil     | Rated     | Set     | Reset   | Coil                          | Rated coil |
|----------|-----------|---------|---------|-------------------------------|------------|
| code     | voltage   | voltage | voltage | resistance                    | power      |
|          | VDC       | VDC     | VDC     | Ω±10%                         | mW         |
| bistable | , 1 coil  |         |         |                               |            |
| A05      | 5         | 3.5     | 2.8     | 62                            | 403        |
| A06      | 6         | 4.2     | 3.3     | 90                            | 400        |
| A12      | 12        | 8.4     | 6.6     | 360                           | 400        |
| A24      | 24        | 16.8    | 13.2    | 1440                          | 400        |
| bistable | , 2 coils |         |         |                               |            |
| F05      | 5         | 3.5     | 2.8     | 42                            | 595        |
| F06      | 6         | 4.2     | 3.3     | 55                            | 655        |
| F12      | 12        | 8.4     | 6.6     | 240                           | 600        |
| F24      | 24        | 16.8    | 13.2    | 886                           | 650        |
| A II C   |           | 201     |         | Contract to the second second | 0000       |

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

#### Bistable coils - operation

| Version                                  | 1  | coil | 2 coils  |
|--|----|------|----------|
| Coil terminals                           | A1 | A2   | A1 A3 A2 |
| Operate                                  | +  | -    | + -      |
| Reset                                    | -  | +    | - +      |
| Contact position not defined at delivery |    |      |          |





| Insulation Data                    |                      |
|------------------------------------|----------------------|
| Initial dielectric strength        |                      |
| between open contacts              | $1000V_{rms}$        |
| between contact and coil           | 5000V <sub>rms</sub> |
| Clearance/creepage                 |                      |
| between contact and coil           | ≥10/10mm             |
| Material group of insulation parts | Illa                 |
| Tracking index of relay base       | PTI 250V             |

#### **Other Data**

Resistance to heat and fire

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

| r toolotai too to r toat ai ia iii o |                     |  |  |
|--------------------------------------|---------------------|--|--|
| WG version                           | according EN60335-1 |  |  |
| Ambient temperature                  | -40 to 85°C         |  |  |
| 0-1                                  |                     |  |  |

Category of environmental protection RTII - flux proof IEC 61810 RTIII - sealed

| Vibration resistance (functional), |                                |
|------------------------------------|--------------------------------|
| form A/form B contact, 30 to 500Hz | 20/5g                          |
| Shock resistance (destructive)     | 100g                           |
| Terminal type                      | PCB-THT, plug-in <sup>2)</sup> |

Weight 14g Resistance to soldering heat THT, IEC 60068-2-20 RTII 270°C/10s RTIII 260°C/5s

Packaging/unit tube/20 pcs., box/500 pcs


2) socket available for 1 coil version only, see Accessories

#### **Accessories**

| For details see datasheet         | Accessories Industrial Power Relay RT2) |
|-----------------------------------|---|
| Socket available for 1 coil versi | on only                                 |

NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.

#### **Dimensions**





## Power PCB Relay RT1 Inrush (Continued)


S0163-BE

S0163-BF


#### PCB layout / terminal assignment

Bottom view on solder pins


#### 16A, 1 form C (CO) contact, pinning 5mm




monostable version



bistable version a)





#### 16A, 1 form A (NO) contact, pinning 5mm



monostable version

S0418-CM






a) Indicated contact position during or after coil energization with reset voltage.


b) for 2 coil version only

S0163DPS


#### 12A, 1 form C (CO) contact, pinning 5mm



monostable version, 1 form C (CO)



monostable version, 1 form A (NO)



L

\*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.

#### Product code structure

Typical product code

3 **RT** 

3

012

#### Type

Power PCB Relay RT1 Inrush

#### Version

16A, pinning 5mm, flux proof Ď 16A, pinning 5mm, sealed

#### Contact configuration

- 3
- 1 form C (CO) contact 1 form A (NO) contact

## **Contact material**

AgNi 90/10 AgSnO<sub>2</sub> K L

# Coil

Coil code: please refer to coil versions table

#### Version

Standard version **Blank** 

WG Product in accordance to IEC 60335-1



## Power PCB Relay RT1 Inrush (Continued)

| Product code | Version          | Contact material   | Coil             | Coil  | Part Number |
|--------------|------------------|--------------------|------------------|-------|-------------|
| RT31L012     | 1 form C (CO)    | AgSnO <sub>2</sub> | Monostable       | 12VDC | 7-1393239-3 |
| RT31L024     | 16A, pinning 5mm |                    |                  | 24VDC | 7-1393239-5 |
| RT31L048     | flux proof       |                    |                  | 48VDC | 7-1393239-6 |
| RT33K012     | 1 form A (NO)    | AgNi 90/10         |                  | 12VDC | 2-1393240-3 |
| RT33K024     | 16A, pinning 5mm |                    |                  | 24VDC | 2-1393240-4 |
| RT33KF12     | flux proof       |                    | Bistable 2 coils | 12VDC | 1-1415540-1 |
| RT33L012     |                  | AgSnO <sub>2</sub> | Monostable       |       | 3-1393240-3 |
| RT33L012WG   |                  |                    |                  |       | 2-1415538-2 |
| RT33L024     |                  |                    |                  | 24VDC | 3-1393240-5 |
| RT33LA12     |                  |                    | Bistable 1 coil  | 12VDC | 2-1393240-7 |
| RT33LA24     |                  |                    |                  | 24VDC | 3-1415379-1 |
| RT33LF12     |                  |                    | Bistable 2 coils | 12VDC | 2-1393240-8 |
| RTD1L005     | 1 form C (CO)    | AgSnO <sub>2</sub> | Monostable       | 5VDC  | 1-1415537-7 |
| RTD1L012     | 16a, pinning 5mm |                    |                  | 12VDC | 5-1393238-6 |
| RTD1L024     | sealed           |                    |                  | 24VDC | 8-1415398-1 |