



SPECIFICATION

(Reference sheet)

· Supplier : Samsung electro-mechanics · Samsung P/N : CL21F104ZBCNNNC

Product : Multi-layer Ceramic Capacitor

Description : CAP, 100nF, 50V, -20/+80%, Y5V, 0805


A. Samsung Part Number

 CL
 21
 F
 104
 Z
 B
 C
 N
 N
 N
 N
 C

 ①
 ②
 ③
 ④
 ⑤
 ⑥
 ⑦
 8
 ⑨
 ⑩
 ⑪

1	Series	Samsung Multi-layer Ceramic Capacitor					
2	Size	0805 (inch code)	L: $2.00 \pm 0.10 \text{ mm}$		W:	$1.25 \pm 0.10 \text{ mm}$	
3	Dielectric	Y5V	8	Inner electrode		Ni	
4	Capacitance	100 nF		Termination		Cu	
5	Capacitance	-20/+80 %		Plating		Sn 100% (Pb Fre	ee)
	tolerance		9	Product		Normal	
6	Rated Voltage	50 V	10	Special		Reserved for future us	е
7	Thickness	$0.85 \pm 0.10 \text{ mm}$	11)	Packaging		Cardboard Type, 7" re-	el

B. Structure & Dimension



Sameung D/N	Dimension(mm)					
Samsung P/N	L	W	Т	BW		
CL21F104ZBCNNNC	2.00 ± 0.10	1.25 ± 0.10	0.85 ± 0.10	0.50 +0.20/-0.30		

C. Samsung Reliablility Test and Judgement Condition

	Judgement	Test condition			
Capacitance	Within specified tolerance	1kHz ±10% / 1.0±0.2Vrms			
Tan δ (DF)	0.05 max.	*A capacitor prior to measuring the capacitance is heat treated at 150 ℃ +0/-10 ℃ for 1 hour and maintained in ambient air for 24±2 hours.			
Insulation 10,000Mohm or 500Mohm× <i>µ</i> F		Rated Voltage 60~120 sec.			
Resistance	Whichever is smaller				
ppearance No abnormal exterior appearance		Microscope (×10)			
Withstanding	No dielectric breakdown or	250% of the rated voltage			
Voltage	mechanical breakdown				
Temperature	Y5V	•			
Characteristics	(From-30 ℃ to 85 ℃, Capacitance change s	should be within -82~+22%)			
Adhesive Strength	No peeling shall be occur on the	500g·f, for 10±1 sec.			
of Termination	terminal electrode				
Bending Strength	Capacitance change: within ±30%	Bending to the limit (1mm)			
		with 1.0mm/sec.			
Solderability	More than 75% of terminal surface	SnAg3.0Cu0.5 solder			
,	is to be soldered newly	245±5°C, 3±0.3sec.			
		(preheating : 80~120°C for 10~30sec.)			
Resistance to	Capacitance change : within ±20%	Solder pot : 270±5°C, 10±1sec.			
Soldering Heat	Tan δ, IR : initial spec.				
Vibration Test	Capacitance change : within \pm 20% Tan δ , IR : initial spec.	Amplitude: 1.5mm From 10Hz to 55Hz (return: 1min.) 2hours × 3 direction (x, y, z)			
Moisture Resistance	Capacitance change : within ±30% Tan δ : 0.09 max	With rated voltage 40±2°C, 90∼95%RH, 500+12/-0hrs			
	IR: 500Mohm or 25Mohm × μ F Whichever is smaller				
High Temperature	Capacitance change : within ±30%	With 200% of the rated voltage			
Resistance	Tan δ : 0.09 max	Max. operating temperature			
	IR: 1,000Mohm or 50Mohm × μ F Whichever is smaller	1000+48/-0hrs			
Temperature	Capacitance change: within ±20%	1 cycle condition			
Cycling	Tan δ, IR : initial spec.	Min. operating temperature → 25°C			
		→ Max. operating temperature → 25°C			
		5 cycle test			

X The reliability test condition can be replaced by the corresponding accelerated test condition.

D. Recommended Soldering method:

Reflow (Reflow Peak Temperature : 260+0/-5°C, 10sec. Max)



A Product specifications included in the specifications are effective as of March 1, 2013.

Please be advised that they are standard product specifications for reference only.

We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications,

please contact our sales personnel or application engineers.

Disclaimer & Limitation of Use and Application

The products listed in this Specification sheet are **NOT** designed and manufactured for any use and applications set forth below.

Please note that any misuse of the products deviating from products specifications or information provided in this Spec sheet may cause serious property damages or personal injury.

We will **NOT** be liable for any damages resulting from any misuse of the products, specifically including using the products for high reliability applications as listed below.

If you have any questions regarding this 'Limitation of Use and Application', you should first contact our sales personnel or application engineers.

- ① Aerospace/Aviation equipment
- 2 Automotive or Transportation equipment (vehicles, trains, ships, etc)
- 3 Medical equipment
- 4 Military equipment
- ⑤ Disaster prevention/crime prevention equipment
- 6 Power plant control equipment
- Atomic energy-related equipment
- Undersea equipment
- Traffic signal equipment
- Data-processing equipment
- ## Electric heating apparatus, burning equipment
- Safety equipment
- ® Any other applications with the same as or similar complexity or reliability to the applications