



Klein Tools CL310 is an automatically ranging true mean squared (TRMS) digital clamp meter that measures AC current via the clamp, and measures AC/DC voltage, resistance, continuity, frequency and capacitance. It also tests diodes via test-leads, as well as temperature via a thermocouple probe. It is no longer in production. Please refer to the CL312 as an equivalent replacement.

Specifications

Application:	Measures AC current	Special Features:	Features low-battery indicator
Batteries:	3 x AAA	Jaw Size:	1-1/8" (28.6 mm)
Drop Protection:	3.3 ft (1 m)	Display:	4,000-count LCD
Voltage:	600 V AC; 600 V DC	Frequency:	10 Hz-1 MHz
Current:	400A	Capacitance:	4000 μ F
Ohms (Resistance):	40MO	Temperature Range:	-40 °F-1,832 °F (-40 °C-1,000 °C)
Standard:	CAT III 600 V; CE certified	Included:	Carrying case, 41" (1041.4 mm) test leads, thermocouple with adaptor, and batteries
Overall Length:	8-45/64" (221.1 mm)	Overall Height:	1-39/64" (40.9 mm)
Overall Width:	3-1/64" (76.6 mm)	Weight:	0.63 lb (0.29 kg)