



SAFETY DATA SHEET

Multi Screen Clene and Cloth

According to Regulation (EC) No 1907/2006, Annex II, as amended.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Multi Screen Clene and Cloth

Product number AMCA_200MIF, ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier

AF INTERNATIONAL. A division of HK WENTWORTH LTD
 ASHBY PARK
 COALFIELD WAY
 ASHBY de la ZOUCH
 LEICESTERSHIRE. LE65 1JR
 UNITED KINGDOM
 +44 (0) 1530 419600
 +44 (0) 1530 416640
 info@hkw.co.uk

1.4. Emergency telephone number

Emergency telephone +44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

2.2. Label elements

Hazard statements EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

Precautionary statements P102 Keep out of reach of children.

Detergent labelling Contains BENZISOTHIAZOLINONE, METHYLISOTHIAZOLINONE, METHYLCHLOROISOTHIAZOLINONE AND METHYLISOTHIAZOLINONE

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

Multi Screen Clene and Cloth

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Composition comments None of the ingredients are required to be listed.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.

Inhalation No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues.

Ingestion No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues.

Skin contact No specific recommendations. Rinse with water. Get medical attention if any discomfort continues.

Eye contact Rinse with water. Get medical attention if any discomfort continues.

Protection of first aiders Use protective equipment appropriate for surrounding materials.

4.2. Most important symptoms and effects, both acute and delayed

General information The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation No specific symptoms known. Spray/mists may cause respiratory tract irritation.

Ingestion No specific symptoms known. May cause discomfort if swallowed.

Skin contact No specific symptoms known. May cause discomfort.

Eye contact No specific symptoms known. May be slightly irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor Treat symptomatically.

Specific treatments No special treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up.

Hazardous combustion products Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Multi Screen Clene and Cloth

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions No specific recommendations. For personal protection, see Section 8.

6.2. Environmental precautions

Environmental precautions Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid discharge to the aquatic environment.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions No specific recommendations.

Storage class Unspecified storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

Ethanol

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Appropriate engineering controls No specific ventilation requirements.

Multi Screen Clene and Cloth

Eye/face protection	No specific eye protection required during normal use. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Not regarded as dangerous for the environment.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	No characteristic odour.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.997
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.

Multi Screen Clene and Cloth

Oxidising properties Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid There are no known conditions that are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects Not regarded as a health hazard under current legislation.

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Multi Screen Clene and Cloth

Carcinogenicity	Based on available data the classification criteria are not met.
IARC carcinogenicity	Contains a substance/a group of substances which may cause cancer. IARC Group 1 Carcinogenic to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Aspiration hazard	Based on available data the classification criteria are not met.
General information	
	No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
Ingestion	No specific symptoms known. May cause discomfort if swallowed.
Skin contact	No specific symptoms known. May cause discomfort.
Eye contact	No specific symptoms known. May be slightly irritating to eyes.
Route of entry	Ingestion Inhalation Skin and/or eye contact
Target organs	No specific target organs known.

Ethanol

Toxicological effects	Not regarded as a health hazard under current legislation.
<u>Acute toxicity - oral</u>	
Notes (oral LD₅₀)	LD ₅₀ 10470 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Acute toxicity - inhalation</u>	
Notes (inhalation LC₅₀)	LD ₅₀ 124.7 mg/l, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Skin corrosion/irritation</u>	
Animal data	Dose: 0.2 mL, 24 hours, Rabbit Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.
<u>Skin sensitisation</u>	
Skin sensitisation	Local Lymph Node Assay (LLNA) - Mouse: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Multi Screen Clene and Cloth

Genotoxicity - in vivo	Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
IARC carcinogenicity	IARC Group 1 Carcinogenic to humans.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Two-generation study - NOAEL 15% , Oral, Mouse REACH dossier information. Based on available data the classification criteria are not met.
Reproductive toxicity - development	Maternal toxicity: - NOAEL: 16000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	LOAEL ~4000 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

SECTION 12: Ecological Information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

12.1. Toxicity

Toxicity Based on available data the classification criteria are not met.

Ethanol

Toxicity	Based on available data the classification criteria are not met.
Acute toxicity - fish	LC ₅₀ , 96 hours: 14200 mg/l, Pimephales promelas (Fat-head Minnow)
Acute toxicity - aquatic invertebrates	LC ₅₀ , 48 hours: 5012 mg/l, Ceriodaphnia dubia
Acute toxicity - aquatic plants	EC ₅₀ , 72 hours: 11.5 mg/l, Chlorella vulgaris
Chronic toxicity - aquatic invertebrates	NOEC, 9 days: 9.6 mg/l, Daphnia magna

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Ethanol

Persistence and degradability	The substance is readily biodegradable.
Biodegradation	Water - Degradation 74%: 10 days
Chemical oxygen demand	1.99 g O ₂ /g substance

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
Partition coefficient	Not available.

Multi Screen Clene and Cloth

Ethanol

Bioaccumulative potential Bioaccumulation is unlikely.

Partition coefficient log Pow: -0.35

12.4. Mobility in soil

Mobility No data available.

Ethanol

Mobility The product is soluble in water.

Surface tension 24.5 mN/m @ 20°C/68°F

12.5. Results of PBT and vPvB assessment

Ethanol

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current EU criteria.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Multi Screen Clene and Cloth

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	Health and Safety at Work etc. Act 1974 (as amended). The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
EU legislation	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 453/2010 of 20 May 2010. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Dangerous Preparations Directive 1999/45/EC. Dangerous Substances Directive 67/548/EEC.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Training advice	Read and follow manufacturer's recommendations.
Issued by	Bethan Massey
Revision date	24/05/2016
Revision	1
SDS number	206
Hazard statements in full	H225 Highly flammable liquid and vapour. EUH208 Contains 1,2-Benzisothiazol-3(2H)-one, Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.